


RECOMMENDED PCB LAYOUT
 TOLERANCE: ±0.05 (TOP VIEW)

- NOTE:
- MATERIAL:
 HOUSING/SLIDE CAM: LCP WITH 10% GF, UL 94V-0, BLACK COLOR.
 CONTACTS: PHOSPHOR BRONZE.
 SHELL: STAINLESS STEEL.
 COIL SPRING: STEEL.
 CAM ROD: STAINLESS STEEL.
 - FINISH:
 CONTACTS: 0.762µm [30u"] MIN. GOLD PLATED ON CONTACT AREA.
 2.54µm [100u"] MIN. MATTE TIN ON SOLDER TAIL,
 1.27µm [50u"] MIN. NICKEL PLATING OVER ALL.
 SHELL: GOLD FLASH AU PLATED ON SOLDER TAILS.
 1.27µm [50u"] MIN. NICKEL PLATING OVER ALL.
 WRITE PROTECT: 0.381µm [15u"] MIN. GOLD PLATED ON CONTACT AREA.
 4.06µm [160u"] MIN. MATTE TIN ON SOLDER TAIL,
 1.27µm [50u"] MIN. NICKEL PLATING OVER ALL.
 - FINISH:
 CONTACTS: 0.381µm [15u"] MIN. GOLD PLATED ON CONTACT AREA.
 2.54µm [100u"] MIN. MATTE TIN ON SOLDER TAIL,
 1.27µm [50u"] MIN. NICKEL PLATING OVER ALL.
 SHELL: GOLD FLASH AU PLATED ON SOLDER TAILS.
 1.27µm [50u"] MIN. NICKEL PLATING OVER ALL.
 WRITE PROTECT: 0.381µm [15u"] MIN. GOLD PLATED ON CONTACT AREA.
 4.06µm [160u"] MIN. MATTE TIN ON SOLDER TAIL,
 1.27µm [50u"] MIN. NICKEL PLATING OVER ALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TEST SPEC.
 109-201, CONDITION B.

DAT2	PIN 9
CD/DAT3	PIN 1
CMD	PIN 2
VSS	PIN 3
VDD	PIN 4
CLK	PIN 5
VSS	PIN 6
DAT0	PIN 7
DAT1	PIN 8
PIN ASSIGNMENT	



REEL	2041353-4	
TRAY	2041353-3	
REEL	2041353-2	
TRAY	2041353-1	
FINISH	PACKAGING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN J. LAI 13JAN2011	TE Connectivity
	0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± - ± 3' ANGLES ± - ± 3'	CHK S. CHIEN 13JAN2011 APVD W. KODAMA 13JAN2011 PRODUCT SPEC 108-57860 APPLICATION SPEC	
MATERIAL SEE NOTE	FINISH SEE NOTE	WEIGHT 2.09 GRAMS CUSTOMER DRAWING	SIZE A3 CAGE CODE 00779 DRAWING NO C=2041353 RESTRICTED TO - SCALE - SHEET 1 OF 3 REV A3

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION AUG ,2006.

© COPYRIGHT 2009 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.





LOC DW
DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			




NOTE:
 1.MATERIAL:
 TRAY: PET
 CARTON: CORRUGATED PAPER
 BAG : PE
 2.DIMENSION:
 TRAY: L=385mm, W=255mm
 CARTON: L=410mm, W=280mm, H=145mm
 3.QUANTITY:
 50 PCS/TRAY; 21 TRAY/CARTON (TOP TRAY IS EMPTY)
 4.WEIGHT
 (SEE TABLE)





5.75 Kg	3.6	50	21	1000 PCS
G/W (kg)	N/W (kg)	PCS/TRAY	TRAYS /CARTON	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	STE TE Connectivity		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME		
0 PLC ±		PRODUCT SPEC	SECURE DIGITAL CARD CONNECTOR		
1 PLC ±		APPLICATION SPEC	H=2.85, SMT TYPE		
2 PLC ±		WEIGHT	SIZE	CAGE CODE	DRAWING NO
3 PLC ±			A3	00779	C=2041353
4 PLC ±			RESTRICTED TO		
ANGLES ±			CUSTOMER DRAWING		
FINISH			SCALE	SHEET	REV
				2 OF 3	A3



- NOTE:
 1. MATERIAL :
 CARTON : CORRUGATED FIBERBOARD
 COVER : PET
 CARRIR TAPE : PS
 REEL : PS
 BAG : PE
 2. PEELING STRENGTH : 0.1~1.3N(10~130 GRAMS)
 3. PEELING SPEED: 300mm/MINUTES.
 4. EACH BAG SHALL BE INCLUDED DESICCANT.



8.72	6.57	450	7	3150
G/W (Kg)	N/W (kg)	PCS/ TAPE	REELS/ CARTON	QUANTITY (PCS)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	TE Connectivity	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CHK	NAME SECURE DIGITAL CARD CONNECTOR H=2.85, SMT TYPE	
MATERIAL	FINISH	APVD	SIZE	RESTRICTED TO
		PRODUCT SPEC	A3	
		APPLICATION SPEC	00779	
		WEIGHT	C=2041353	
		CUSTOMER DRAWING	SCALE	SHEET 3 OF 3 REV A3