


2 - 382568 - 0

Product Details



2 - 382568 - 0

 [Active](#)

DIP Sockets

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? DIP Socket
- ? Number of Positions = 20
- ? Row-to-Row Spacing = 7.87 mm
- ? Thru Hole
- ? Mount Style = Vertical

[View all Features](#) | [Find Similar Products](#)

 **Live Product Chat** US Only
8:30am - 5pm ET, Mon - Fri

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: ? SOCKET ASSY, DIP, SPCL LUBE, DIPLOMATE DL - (PDF, English) Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? DIPLOMATE DL (Dual Leaf) DIP Sockets (PDF, English) ? Diplomate DL (Dual -Leaf) Dip Socket (PDF, English) Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Product Type = DIP Socket ? Number of Positions = 20 ? Profile = Standard ? Frame Style = Closed ? Leg Style = Straight ? Proprietary Name = DIPLOMATE DL ? Color = Black ? Qty./Tube = 21 ? Qty. Tubes/Box = 100 ? Product Series = Standard ? Comment = ONLY sockets with straight solder tails are recommended for automatic insertion. Electrical Characteristics: ? Insulation Resistance (M?) = 10,000 ? Contact Resistance (m?) = 30 Termination Related Features: ? Termination (Solder) Post Length (mm [in]) = 3.25 [0.128] Body Related Features: ? Row-to-Row Spacing (mm [in]) = 7.87 [0.310] ? Mount Style = Vertical ? Centerline (mm [in]) = 2.54 [0.100] Contact Related Features: ? Contact Mount = Thru Hole ? Contact Material = Phosphor Bronze ? Contact Mating Area Plating = Tin ? Contact Style = Stamped + Formed ? Mating Contact Type = Dual Leaf	Housing Related Features: ? Housing Material = Thermoplastic Glass reinforced ? Housing Flammability Rating = UL 94V -0 Configuration Related Features: ? Height Above PC Board (mm [in]) = 5.33 [0.210] Industry Standards: ? RoHS/ELV Compliance = RoHS compliant, ELV compliant ? Lead Free Solder Processes = Wave solder capable to 240°C ? RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: ? Temperature Range (°C) = 105 Operation/Application: ? Application = Production Packaging Related Features: ? Packaging Method = Tube Other: ? Brand = AMP