

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5013310207

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Vertical, Surface Mount, Tin Plated, Friction Lock, 2 Circuits, Natural



|                                                               |                                                                   |
|---------------------------------------------------------------|-------------------------------------------------------------------|
| <b>Documents:</b>                                             |                                                                   |
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">Product Specification 5013301000-PS-004 (PDF)</a>     |
| <a href="#">3D Model</a>                                      | <a href="#">Application Specification 5013300000-AS-000 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                | <a href="#">Packaging Specification SPK-501331-001-001 (PDF)</a>  |
| <a href="#">Product Specification 5013300000-PS-001 (PDF)</a> | <a href="#">Datasheet (PDF)</a>                                   |
| <a href="#">Product Specification 5013301000-PS-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>              |
| <a href="#">Product Specification 5013301000-PS-003 (PDF)</a> |                                                                   |

|                                |                                     |
|--------------------------------|-------------------------------------|
| <b>Agency Certification</b>    |                                     |
| UL                             | E29179                              |
| <b>General</b>                 |                                     |
| Product Family                 | PCB Headers                         |
| Series                         | 501331                              |
| Application                    | Signal, Wire-to-Board               |
| Overview                       | Pico-Clasp Wire-to-Board Connectors |
| Product Name                   | Pico-Clasp                          |
| Taxonomy                       | PCB Headers and Receptacles         |
| UPC                            | 822348542772                        |
| <b>Physical</b>                |                                     |
| Breakaway                      | No                                  |
| Circuits (Loaded)              | 2                                   |
| Circuits (maximum)             | 2                                   |
| Color - Resin                  | Natural                             |
| Durability (mating cycles max) | 30                                  |
| First Mate / Last Break        | No                                  |
| Glow-Wire Capable              | No                                  |
| Guide to Mating Part           | No                                  |
| Keying to Mating Part          | None                                |
| Lock to Mating Part            | Yes                                 |
| Material - Metal               | Phosphor Bronze                     |
| Material - Plating Mating      | Tin                                 |
| Material - Plating Termination | Tin                                 |
| Material - Resin               | Nylon                               |
| Net Weight                     | 74.700/mg                           |
| Number of Rows                 | 1                                   |
| Orientation                    | Vertical                            |
| PCB Locator                    | No                                  |
| PCB Retention                  | Yes                                 |
| Packaging Type                 | Embossed Tape on Reel               |
| Pitch - Mating Interface       | 1.00mm                              |
| Polarized to Mating Part       | Yes                                 |
| Polarized to PCB               | No                                  |
| Robotic Placement              | Vacuum Pick-Up Tape                 |
| Shrouded                       | Fully                               |
| Stackable                      | No                                  |
| Temperature Range - Operating  | -40° to +105°C                      |
| Termination Interface: Style   | Surface Mount                       |
| <b>Electrical</b>              |                                     |

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b>                                                 |                   |
| Not Relevant                                                  |                   |
| <b>EU RoHS</b>                                                | <b>China RoHS</b> |
| Compliant                                                     |                   |
| <b>REACH SVHC</b>                                             |                   |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |                   |
| <b>Halogen-Free</b>                                           |                   |
| <b>Status</b>                                                 |                   |
| Not Low-Halogen                                               |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Green Image       |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Contained     |

Search Parts in this Series

501331 Series

Mates With

501330 Pico-Clasp Wire-to-Board Female Housing

Current - Maximum per Contact

2.0A

Voltage - Maximum

100V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification

5013300000-AS-000

Packaging Specification

SPK-501331-001-001

Product Specification

5013300000-PS-001, 5013301000-PS-001,  
5013301000-PS-003, 5013301000-PS-004

Sales Drawing

5013310000-SD-000

This document was generated on 10/19/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**