


Product Details for 5535661 - 1



5535661 - 1

[Active](#)

PC Card (PCMCIA) Connectors & Accessories

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Guide Rail
- ? Non - CardBus Application
- ? Guide Rail Type = Left Guide
- ? Number of Positions = 68
- ? Single/Double Slot = Single

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [GUIDE RAILS, RAISED, EXTENDED, WITH THRU -HOLE HOLDDO...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Guide Rail
- ? [Number of Positions](#) = 68
- ? [Card Guide Side](#) = Left
- ? [Shielded](#) = No
- ? [Mating Polarization](#) = Without
- ? Holddowns = With
- ? Holddown Material = Phosphor Bronze
- ? Rail Material = Liquid Crystal Polymer (LCP)
- ? Color = Black

Mechanical Attachment:

- ? Holddown Plating = Tin

Body Related Features:

- ? [Guide Rail Type](#) = Left Guide
- ? [Single/Double Slot](#) = Single

Contact Related Features:

- ? Region = Americas

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant
- ? Height = Raised

Operation/Application:

- ? [Application](#) = Non - CardBus

Other:

- ? Brand = AMP