


## 63962 -1 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**63962 -1**

✓ [Active](#)

### FASTON Uninsulated Receptacles & Housings

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Receptacle
- ? Tab Fit = 6.35 x 0.81 mm
- ? Board Mount
- ? Receptacle Style = Straight
- ? Non - Insulation Support

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [RECEPTACLE, FASTIN-FASTON,.250 SERIES](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? [FASTIN-FASTON 110, 187, 205 And 312 Series Receptacl...](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Receptacle
- ? [Tab Fit \(mm \[in\]\)](#) = 6.35 x 0.81 [.250 x .032]
- ? [Receptacle Style](#) = Straight
- ? [Insulation Support](#) = Non - Insulation Support
- ? [Insertion Force](#) = Low
- ? [Material](#) = Brass
- ? [Finish](#) = Tin

#### Mechanical Attachment:

- ? [Board Mount](#) = Yes

#### Body Related Features:

- ? [Weld Tab](#) = Without

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece

#### Other:

- ? [For Hermetic Header Tab](#) = No
- ? [Line](#) = FASTON .250
- ? Brand = AMP