


<b>DRAWING NUMBER:</b>	<b>09-9060-1-XXXX</b>
<b>PRODUCT GROUP:</b>	PC JACKS
<b>SUB-GROUP:</b>	INSULATED PC JACKS
<b>DESCRIPTION:</b>	PC JACK - PTFE INSULATED



ACCEPTS PIN / PLUG / JACK SIZE	OVERALL LENGTH	MIN. HOLE DEPTH	MOUNTING ORIENTATION
0.080" ± 0.001	0.688"	0.332"	VERTICAL
BOARD / PANEL MOUNTING METHOD	MOUNTING HOLE SIZE	BOARD / PANEL THICKNESS	FEED THRU COMBINATION
PRESS FIT	0.203" ± 0.002	1/32" - 23/64"	JACK/EYELET

**PART NO. STRUCTURE:**

<b>09-9060</b>	-	<b>1</b>	-	<b>XX</b>	<b>XX</b>
PART SERIES		DIMENSION		FINISH	INSULATION COLOR

**MATERIAL OPTIONS:**

**09-9060-1-XXXX**

COMPONENT	MATERIAL	MATERIAL AND SPECIFICATION
<b>BODY</b>	BRASS	BRASS PER ASTM B16, ALLOY C36000, 1/2 HARD
<b>SPRING (CAGE)</b>	BERYLLIUM COPPER	BERYLLIUM COPPER PER ASTM B194, ALLOY C17200
<b>INSULATION*</b>	PTFE	PTFE PER ASTM D1710
<b>MOUNTING BRACKET</b>	N/A	N/A

\*For Insulation color, please see INSULATION COLOR OPTIONS on Page 2

FINISH - PLATING OPTIONS:

09-9060-1-XXXX

FINISH CODE	COMPONENT	FINISH	FINISH AND SPECIFICATION
03	BODY	GOLD	0.000010"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	SPRING (CAGE)	GOLD	0.000030"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	MOUNTING BRACKET	N/A	N/A
035	BODY	GOLD	0.000020"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	SPRING (CAGE)	GOLD	0.000050"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	MOUNTING BRACKET	N/A	N/A
04	BODY	ELECTRO-TIN	0.000100"MIN. ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	SPRING (CAGE)	BRIGHT ELECTRO-TIN	0.000200"MIN. BRIGHT ELECTRO-TIN PER ASTM B545 OVER 0.000050"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	MOUNTING BRACKET	N/A	N/A
06	BODY	ELECTRO-TIN	0.000100"MIN. ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	SPRING (CAGE)	GOLD	0.000030"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	MOUNTING BRACKET	N/A	N/A
063	BODY	BRIGHT TIN-LEAD	0.000200"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	SPRING (CAGE)	GOLD	0.000030"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	MOUNTING BRACKET	N/A	N/A
088	BODY	BRIGHT TIN-LEAD	0.000200"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	SPRING (CAGE)	BRIGHT TIN-LEAD	0.000200"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. NICKEL PER SAE-AMS-QQ-N-290, CLASS 2
	MOUNTING BRACKET	N/A	N/A

INSULATION COLOR OPTIONS:

09-9060-1-XXXX

INSULATION COLOR	BLACK	BLUE	BROWN	GRAY	GREEN	ORANGE	RED	VIOLET	WHITE	YELLOW
COLOR CODE NO.	10	16	11	18	15	13	12	17	19	14

TOLERANCES:\*

DECIMAL	FRACTIONAL	ANGULAR	DRAWING ORIGATION DATE	LAST MODIFICATION DATE
± 0.010	± 1/64	N/A	3/20/1997	1/1/2017

\*All dimensions are in inches.

RoHS COMPLIANCE:

09-9060-1-03XX

PART NUMBER	RoHS COMPLIANT
09-9060-1-0310	YES
09-9060-1-0311	NO
09-9060-1-0312	NO
09-9060-1-0313	NO
09-9060-1-0314	NO
09-9060-1-0315	YES
09-9060-1-0316	YES
09-9060-1-0317	YES
09-9060-1-0318	NO
09-9060-1-0319	YES

09-9060-1-035XX

PART NUMBER	RoHS COMPLIANT
09-9060-1-03510	YES
09-9060-1-03511	NO
09-9060-1-03512	NO
09-9060-1-03513	NO
09-9060-1-03514	NO
09-9060-1-03515	YES
09-9060-1-03516	YES
09-9060-1-03517	YES
09-9060-1-03518	NO
09-9060-1-03519	YES

09-9060-1-04XX

PART NUMBER	RoHS COMPLIANT
09-9060-1-0410	YES
09-9060-1-0411	NO
09-9060-1-0412	NO
09-9060-1-0413	NO
09-9060-1-0414	NO
09-9060-1-0415	YES
09-9060-1-0416	YES
09-9060-1-0417	YES
09-9060-1-0418	NO
09-9060-1-0419	YES

09-9060-1-06XX

PART NUMBER	RoHS COMPLIANT
09-9060-1-0610	YES
09-9060-1-0611	NO
09-9060-1-0612	NO
09-9060-1-0613	NO
09-9060-1-0614	NO
09-9060-1-0615	YES
09-9060-1-0616	YES
09-9060-1-0617	YES
09-9060-1-0618	NO
09-9060-1-0619	YES

09-9060-1-063XX

PART NUMBER	RoHS COMPLIANT
09-9060-1-06310	NO
09-9060-1-06311	NO
09-9060-1-06312	NO
09-9060-1-06313	NO
09-9060-1-06314	NO
09-9060-1-06315	NO
09-9060-1-06316	NO
09-9060-1-06317	NO
09-9060-1-06318	NO
09-9060-1-06319	NO

09-9060-1-088XX

PART NUMBER	RoHS COMPLIANT
09-9060-1-08810	NO
09-9060-1-08811	NO
09-9060-1-08812	NO
09-9060-1-08813	NO
09-9060-1-08814	NO
09-9060-1-08815	NO
09-9060-1-08816	NO
09-9060-1-08817	NO
09-9060-1-08818	NO
09-9060-1-08819	NO

MILITARY REFERENCE SPECIFICATIONS:

09-9060-1-03XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-0310	N/A	N/A
09-9060-1-0311	N/A	N/A
09-9060-1-0312	N/A	N/A
09-9060-1-0313	N/A	N/A
09-9060-1-0314	N/A	N/A
09-9060-1-0315	N/A	N/A
09-9060-1-0316	N/A	N/A

09-9060-1-035XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-03510	N/A	N/A
09-9060-1-03511	N/A	N/A
09-9060-1-03512	N/A	N/A
09-9060-1-03513	N/A	N/A
09-9060-1-03514	N/A	N/A
09-9060-1-03515	N/A	N/A
09-9060-1-03516	N/A	N/A

Continued on next page...

MILITARY REFERENCE SPECIFICATIONS CONTINUED:

09-9060-1-03XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-0317	N/A	N/A
09-9060-1-0318	N/A	N/A
09-9060-1-0319	N/A	N/A

09-9060-1-04XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-0410	N/A	N/A
09-9060-1-0411	N/A	N/A
09-9060-1-0412	N/A	N/A
09-9060-1-0413	N/A	N/A
09-9060-1-0414	N/A	N/A
09-9060-1-0415	N/A	N/A
09-9060-1-0416	N/A	N/A
09-9060-1-0417	N/A	N/A
09-9060-1-0418	N/A	N/A
09-9060-1-0419	N/A	N/A

09-9060-1-063XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-06310	N/A	N/A
09-9060-1-06311	N/A	N/A
09-9060-1-06312	N/A	N/A
09-9060-1-06313	N/A	N/A
09-9060-1-06314	N/A	N/A
09-9060-1-06315	N/A	N/A
09-9060-1-06316	N/A	N/A
09-9060-1-06317	N/A	N/A
09-9060-1-06318	N/A	N/A
09-9060-1-06319	N/A	N/A

09-9060-1-035XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-03517	N/A	N/A
09-9060-1-03518	N/A	N/A
09-9060-1-03519	N/A	N/A

09-9060-1-06XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-0610	N/A	N/A
09-9060-1-0611	N/A	N/A
09-9060-1-0612	N/A	N/A
09-9060-1-0613	N/A	N/A
09-9060-1-0614	N/A	N/A
09-9060-1-0615	N/A	N/A
09-9060-1-0616	N/A	N/A
09-9060-1-0617	N/A	N/A
09-9060-1-0618	N/A	N/A
09-9060-1-0619	N/A	N/A

09-9060-1-088XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER
09-9060-1-08810	N/A	N/A
09-9060-1-08811	N/A	N/A
09-9060-1-08812	N/A	N/A
09-9060-1-08813	N/A	N/A
09-9060-1-08814	N/A	N/A
09-9060-1-08815	N/A	N/A
09-9060-1-08816	N/A	N/A
09-9060-1-08817	N/A	N/A
09-9060-1-08818	N/A	N/A
09-9060-1-08819	N/A	N/A

TOOLING:

INSTALLATION TOOL: ARBOR PRESS	INSTALLATION TOOL: ANVIL (ARBOR PRESS OPERATED)	INSTALLATION TOOL: PRESS-FIT / ROLL SWAGE / RIVET PUNCH (ARBOR PRESS OPERATED)	INSTALLATION TOOL: PRESS-FIT (HAND OPERATED)	CRIMPING TOOL (COMMERCIAL VERSION - 701-2860 WITH CRIMPING DIE RANGE 10-22)
TM1	TA09-9060	TPP09-9060	TTJ09-9060	N/A

NOTES:

---

**DATASHEET NOTES**

CLOSED ENTRY CAGE.

---

**INSTRUCTION NOTES**

SEE GENERAL PRESS FIT INSTALLATION INSTRUCTION ON CONCORD ELECTRONICS' WEBSITE [WWW.CONCORD-ELECTRONICS.COM](http://WWW.CONCORD-ELECTRONICS.COM)

---