


827297 -3 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



827297 -3

[Active](#)

.100 inch AMPMODU Headers

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Header
- ? Header Type = Shrouded
- ? Number of Rows = Dual
- ? Number of Positions = 6
- ? Mating Post Length = 6.70 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version O)
- ? [3D Model](#) (IGES, Version O)
- ? [3D Model](#) (STEP, Version O)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Header
- ? [Number of Positions](#) = 6
- ? [Mount Angle](#) = Vertical
- ? [PCB Retention Feature](#) = No
- ? [Surface Mount Compatible](#) = Yes
- ? [Board Standoff](#) = With
- ? [Mounting Ears](#) = Without
- ? [Mating Connector Lock](#) = With
- ? [Mating Connector Lock Type](#) = Detent Latching
- ? [Housing Style](#) = Open End / Open End
- ? Post Size (mm [in]) = 0.64 [.025]
- ? Profile = Standard

Mechanical Attachment:

- ? Mating Post Length (mm [in]) = 6.70 [0.264]
- ? [Panel Attachment](#) = Without

Termination Related Features:

- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.20 [0.126]
- ? Solder Tail Contact Plating = Tin over Nickel

Body Related Features:

- ? [Header Type](#) = Shrouded
- ? [Number of Rows](#) = Dual
- ? [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]
- ? [Selectively Loaded](#) = No
- ? [Mount Type](#) = PC Board

Contact Related Features:

- ? [Contact Mating Area Plating Material](#) = Tin over Nickel
- ? Contact Shape = Round
- ? Contact Material = Brass

Housing Related Features:

- ? Housing Material = Polyester
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin -in -Paste capable to 245°C, Pin in -Paste capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [High Temperature Housing](#) = Yes
- ? Operating Temperature (°C) = -55 - +105

Operation/Application:

- ? [High Speed Serial Data Connector](#) = No

Other:

- ? Brand = AMP