


P.C. PINS

09-8301-X-03 P.C. PIN .017

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.025 ± .002 DIA (#72 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8301-1-03	.061	.025	(03) GOLD
09-8301-2-03	.075	.040	(03) GOLD

09-8080-2-03 P.C. PIN .018

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.052 DIA (#66 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8080-2-03	.082 2,08	1/16 1,59	(03) GOLD

09-8XXX-XX .020 PINS

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.043 ± .001 DIA (#57 DRILL)




MATERIAL: BRASS

PART NUMBER	H	L	K	S	R	P	BOARD THICKNESS	STANDARD (XX) FINISH
09-8068-1-03	.310 7,87	.051 1,30	.025 0,64	.120 3,05	.020 0,51	.045 1,14	1/32 0,79	(03) GOLD
09-8063-1-05	.453 11,54	.051 1,30	.025 0,64	.120 3,05	.020 0,51	.045 1,14	1/32 0,79	(05) ELECTRO-SOLDER
09-8012-1-03	.540 14,73	.051 1,30	.025 0,64	.120 3,05	.020 0,51	.045 1,14	1/32 0,79	(03) GOLD
09-8012-2-03	.540 14,73	.082 2,08	.025 0,64	.120 3,05	.020 0,51	.045 1,14	1/16 1,59	(03) GOLD
09-8008-2-03	.758 19,85	.082 2,08	.020 0,51	.350 8,89	.230 5,84	.045 1,14	1/16 1,59	(03) GOLD
09-8015-1-03	.950 24,13	.051 1,30	.025 0,64	.120 3,05	.020 0,51	.045 1,14	1/32 0,79	(03) GOLD
09-8065-1-03	1.140 28,94	.051 1,30	.025 0,64	.000 15,74	.045 1,14	.030 0,76	1/32 0,79	(03) GOLD

10-963-2-03 P.C. PIN .020

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.036 DIA (#64 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-963-2-03	.094 2,39	1/16 1,59	(03) GOLD

09-8031-1-03 P.C. PIN .020

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.043 DIA (#57 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8031-1-03	.051 1,30	1/32 0,79	(03) GOLD

09-8058-1-03 P.C. PIN .020

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.043 DIA (#57 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8058-1-03	.051 1,30	1/32 0,79	(03) GOLD

09-81XX-X-XX P.C. PIN .020

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.037 DIA (#63 DRILL)




MATERIAL: BRASS

PART NUMBER	H	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8138-1-05	.040 1,02	.037 0,94	1/64 0,40	
- 1-05	.040 1,02	.053 1,35	1/32 0,79	(05) ELECTRO-SOLDER
- 2-05	.040 1,02	.084 2,13	1/16 1,59	
09-8139-1-05	.060 1,52	.053 1,35	1/32 0,79	(05) ELECTRO-SOLDER
- 2-05	.060 1,52	.084 2,13	1/16 1,59	

09-8XXX-2-03 P.C. PINS .020

BASIC PART NO. FINISH



MATERIAL: BRASS

PART NUMBER	H	L	THICKNESS	(XX) FINISH
09-8090-2-03	.270 6,86	.100 2,54	1/16 1,59	(03) GOLD
09-8017-2-03	.445 11,30	.100 2,54	1/16 1,59	(03) GOLD
09-8187-2-03	.545 13,84	.100 2,54	1/16 1,59	(03) GOLD
09-8001-2-03	.570 14,48	.100 2,54	1/16 1,59	(03) GOLD
09-8018-2-03	.950 24,13	.100 2,54	1/16 1,59	(03) GOLD

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY.

CONCORD


THE COMPONENT PEOPLE

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161

P.C. PINS

09-8XXX-X-XX P.C. PINS .020

BASIC PART NO. FINISH



MATERIAL: BRASS

09-8026 .031 DIA (#68 DRILL)
09-8183 .035 DIA (#65 DRILL)
09-8179 .039 DIA (#61 DRILL)
09-8027 .031 DIA (#68 DRILL)
09-8056 .031 DIA (#68 DRILL)
09-8181 .035 DIA (#65 DRILL)
09-8046 .043 DIA (#57 DRILL)
09-8180 .039 DIA (#61 DRILL)
09-8182 .035 DIA (#65 DRILL)

STANDARD
(XX) FINISH
(05) ELECTRO-
SOLDER
(03) GOLD


PART NUMBER	H	L	D	A	K	M	P	BOARD THICKNESS
09-8026-1-05	.050 1,27	.051 1,30	.027 0,69	.050 1,27	.010 0,25	.018 0,46	.040 1,02	1/32 0,79
-2-05	.050 1,27	.085 2,16	.027 0,69	.050 1,27	.010 0,25	.018 0,46	.040 1,02	1/16 1,59
09-8183-1-05	.125 3,18	.051 1,30	.031 0,79	.050 1,27	.010 0,25	.020 0,51	.040 1,02	1/32 0,79
09-8179-1-03	.125 3,18	.051 1,30	.036 0,91	.050 1,27	.050 1,27	.025 0,64	.040 1,02	1/32 0,79
09-8027-2-05	.130 3,30	.085 2,16	.027 0,69	.050 1,27	.010 0,25	.018 0,46	.040 1,02	1/16 1,59
09-8056-2-03	.160 4,06	.085 2,16	.027 0,69	.050 1,27	.010 0,25	.018 0,46	.040 1,02	1/16 1,59
09-8181-1-05	.225 5,72	.051 1,30	.031 0,79	.050 1,27	.010 0,25	.020 0,51	.040 1,02	1/32 0,79
09-8046-3-05	.275 6,99	.113 2,87	.040 1,02	.062 1,57	.025 0,64	.025 0,64	.035 0,89	3/32 2,38
09-8180-3-03	.350 8,89	.119 3,02	.036 0,91	.050 1,27	.020 0,51	.025 0,64	.045 1,14	3/32 2,38
09-8182-1-05	.375 9,53	.051 1,30	.031 0,79	.050 1,27	.010 0,25	.020 0,51	.040 1,02	1/32 0,79

10-9XX-X-XX .025 PINS

10-8XXX-X-XX
09-8XXX-X-XX

MATERIAL: BRASS

BASIC PART NO. FINISH



RECOMMENDED MOUNTING HOLES
043 ± .001 DIA (#57 DRILL)
062 ± .002 (1/16 DRILL)
035 ± .002 DIA (#65 DRILL)
035 ± .002 DIA (#65 DRILL)
036 ± .002 DIA (#65 DRILL)
052 ± .002 DIA (#55 DRILL)
052 ± .002 DIA (#55 DRILL)
052 ± .002 DIA (#55 DRILL)
035 ± .002 DIA (#65 DRILL)

STANDARD
(XX) FINISH
(03) GOLD OR
(04) ELECTRO-
TIN


PART NUMBER	H	L	D	A	K	M	P	BOARD THICKNESS
10-915-1-03	.150 3,81	.051 1,30	.040 1,02	.062 1,57	.025 0,64	.025 0,64	.035 0,89	1/32 0,79
-2-03	.150 3,81	.082 2,08	.040 1,02	.062 1,57	.025 0,64	.025 0,64	.035 0,89	1/16 1,59
-3-03	.150 3,81	.113 2,87	.040 1,02	.062 1,57	.025 0,64	.025 0,64	.035 0,89	3/32 2,38
-3A-03	.150 3,81	.125 3,18	.040 1,02	.062 1,57	.025 0,64	.025 0,64	.035 0,89	
10-925-1-XX	.155 3,94	.082 1,57	.058 1,47	.078 1,98	.030 0,76	.040 1,02	.040 1,02	1/32 0,79
-2-XX	.155 3,94	.094 2,39	.058 1,47	.078 1,98	.030 0,76	.040 1,02	.062 1,57	1/16 1,59
-3-XX	.155 3,94	.125 3,18	.058 1,47	.078 1,98	.030 0,76	.040 1,02	.062 1,57	3/32 2,38
-4-XX	.155 3,94	.156 3,96	.058 1,47	.078 1,98	.030 0,76	.040 1,02	.062 1,57	1/8 3,18
10-8017-1-03	.170 4,32	.051 1,30	1,031 0,79	.050 1,27	.020 0,51	.020 0,51	.040 1,02	1/32 0,79
-2-03	.170 4,32	.082 2,08	1,031 0,79	.050 1,27	.020 0,51	.020 0,51	.040 1,02	1/16 1,59
10-8018-1-03	.320 8,13	.051 1,30	1,031 0,79	.050 1,27	.020 0,51	.020 0,51	.040 1,02	1/32 0,79
-2-03	.320 8,13	.082 2,08	1,031 0,79	.050 1,27	.020 0,51	.020 0,51	.040 1,02	1/16 1,59
10-8019-1-03	.320 8,13	.051 1,30	1,031 0,79	.050 1,27	.170 4,32	.020 0,51	.040 1,02	1/32 0,79
-2-03	.320 8,13	.082 2,08	1,031 0,79	.050 1,27	.170 4,32	.020 0,51	.040 1,02	1/16 1,59
09-8176-1-03	.437 11,10	.054 1,37	.048 1,22	.062 1,57	.020 0,51	.032 0,81	.031 0,79	1/32 0,79
09-8178-2-03	.437 11,10	.084 2,39	.047 1,19	.062 1,57	.062 1,57	.032 0,81	.031 0,79	1/16 1,59
10-8020-1-03	.570 14,40	.051 1,30	1,031 0,79	.050 1,27	.420 10,67	.020 0,51	.031 0,79	1/32 0,79
-2-03	.570 14,40	.082 2,08	1,031 0,79	.050 1,27	.420 10,67	.020 0,51	.031 0,79	1/16 1,59

* TOLERANCE IS ± .001 (± 0,03) 1 TOLERANCE IS ± .0015 (± 0,04)

09-8172-2-03 P.C. PIN .025

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.0465 DIA (#56 DRILL)




MATERIAL: BRASS

PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8172-2-03	.084 2,13	1/16 1,59	(03) GOLD

14-991-2-03 .025 PIN

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.033 DIA (#66 DRILL)




MATERIAL: RED LEADED BRASS

PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
14-991-2-03	.094 2,39	1/16 1,59	(03) GOLD

09-81XX-1-03 P.C. PIN .025

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.043 DIA (#57 DRILL)




MATERIAL: BRASS

PART NUMBER	H	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8173-1-03	.600 15,24	.051 1,30	1/32 0,79	(03) GOLD
09-8174-1-03	.900 22,86	.051 1,30	1/32 0,79	(03) GOLD

10-9XX-X-XX P.C. PIN .025

09-8170-2-04

RECOMMENDED MOUNTING HOLE
.035 DIA (#65 DRILL)



MATERIAL: BRASS

PART NUMBER	H	L	J	P	BOARD THICKNESS	STANDARD (XX) FINISH
10-964-2-04	.092 2,34	.082 2,08	.067 1,70	.062 1,57	1/16 1,59	(04) ELECTRO-TIN
10-927-1-XX	.213 5,41	.047 1,19	.188 4,78	.031 0,79	1/32 0,79	(03) GOLD OR
-2-XX	.213 5,41	.082 2,08	.188 4,78	.031 0,79	1/16 1,59	(04) ELECTRO-TIN
09-8170-2-04	.337 8,56	.078 1,98	.312 7,92	.031 0,79	1/16 1,59	(04) ELECTRO-TIN

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY.

CONCORD
THE COMPONENT PEOPLE


30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161

P.C. PINS

09-8XXX-X-XX P.C. PIN .031

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE



MATERIAL: BRASS

*FOR 09-8149 IS ±.002


PART NUMBER	H	L	D	A	M	P	BOARD THICKNESS	STANDARD (X) FINISH							
09-8045-1-XX	.170	.432	.051	.138	.040	.082	.070	.178	.025	.084	.040	.182	1/32	0,79	(03)GOLD
2-XX	.170	.432	.082	.138	.040	.082	.070	.178	.025	.084	.040	.182	1/16	1,59	(04)ELECTRO-TIN
3-XX	.170	.432	.113	.138	.040	.082	.070	.178	.025	.084	.040	.182	3/32	2,38	(01)SILVER
09-8149-1-DI	.176	.417	.050	.127	.047	.119	.062	1,57	.020	0,51	.020	0,51	1/32	0,79	(01)SILVER
09-8044-1-XX	.320	.813	.051	.138	.040	.187	.070	.178	.025	.084	.040	.182	1/32	0,79	(03)GOLD
2-XX	.320	.813	.082	.138	.040	.187	.070	.178	.025	.084	.040	.182	1/16	1,59	(04)ELECTRO-TIN
3-XX	.320	.813	.113	.138	.040	.187	.070	.178	.025	.084	.040	.182	3/32	2,38	(01)SILVER
09-8024-1-03	.320	.813	.051	.138	.031	.679	.050	1,27	.015	0,38	.040	.182	1/32	0,79	(03)GOLD

10-849-1-03 P.C. PIN .035

09-81XX-1-03

RECOMMENDED MOUNTING HOLE .0625 DIA (1/16 DRILL)

BASIC PART NO. FINISH




PART NUMBER	H		L		THICKNESS	(XX) FINISH	
10-849-1-03	.130	3,30	.062	1,57	1/32	0,79	(03) GOLD
09-8152-1-03	.155	3,94	.062	1,57	1/32	0,79	(03) GOLD
09-8153-1-03	.180	4,57	.062	1,57	1/32	0,79	(03) GOLD

12-8XX-3-03 P.C. PIN .040

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE .0635 DIA (#52 DRILL)




PART NUMBER	L	C	BOARD THICKNESS	STANDARD (XX) FINISH
12-886-3-03	.125 3,18	.030 0,76	3/32 2,38	(03) GOLD
12-890-3-03	.125 3,18	.040 1,02	3/32 2,38	(03) GOLD

09-81XX-2-03 P.C. PIN .038

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE .064 DIA (#52 DRILL)




PART NUMBER	H	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8150-2-03	.187 4,75	.094 2,39	1/16 1,59	(03) GOLD
09-8151-2-03	.250 6,35	.094 2,39	1/16 1,59	(03) GOLD

09-8XXX-X-XX P.C. PIN .030

BASIC PART NO. FINISH

PN RECOMMENDED MOUNTING HOLE

09-8147 .033 DIA (#66 DRILL)
09-8055 .043 DIA (#57 DRILL)




PART NUMBER	H	L	D	A	K	M	BOARD THICKNESS	STANDARD (XX) FINISH
09-0147-1-04	.421 10,68	.051 1,30	.030 0,76	.062 1,57	.030 0,76	.015 0,38	1/32 0,79	(04)ELECTRO-TIN
09-0055-1-03	.800 15,24	.051 1,30	.040 1,02	.070 1,78	.020 0,51	.025 0,64	1/32 0,79	(03)GOLD
2-03	.800 15,24	.082 2,08	.040 1,02	.070 1,78	.020 0,51	.025 0,64	1/16 1,59	(03)GOLD

10-877-X-05 P.C. PIN .032

BASIC PART NO. FINISH


RECOMMENDED MOUNTING HOLE .055 DIA (#54 DRILL)



PART NUMBER		L	BOARD THICKNESS	STANDARD (XX) FINISH
10-877-1-05		.051 1,30	1/32 0,79	(05) ELECTRO-SOLDER
2-05		.082 2,08	1/16 1,59	
3-05		.113 2,87	3/32 2,38	

09-0008-1-03 P.C. PIN .030

BASIC PART NO. FINISH



MATERIAL: BRASS

PART NUMBER


STANDARD (XX) FINISH

09-0008-1-03

(03) GOLD

12-8XX-1-03 P.C. PIN MOLDED

BASIC PART NO. FINISH



															STANDARD		
PART NUMBER	H	L	C	A	D	K	S	M	P	(XX) FINISH							
12-887-1-03	.250	6,35	.065	1,63	.023	0,58	.082	1,57	.040	1,02	.025	0,64	.025	0,64	.040	1,02	(03) GOLD
12-885-1-03	.270	6,86	.125	3,18	.103	0,76	.094	2,39	.080	1,57	.030	0,76	.030	0,76	.040	1,02	100 2,54
																	M ±.001 (±0,03) L ±.002 (±0,05)

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY.

CONCORD

THE COMPONENT PEOPLE

30 GREAT JONES STREET

NEW YORK, N.Y. 10012-1115

(212) 777-6571 • FAX (212) 995-0161


P.C. PINS

10-8XX-X-XX P.C. PIN .030 09-8XXX-X-XX

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)

MATERIAL: BRASS




PART NUMBER	H	L	P	BOARD THICKNESS	STANDARD (XX) FINISH
10-865-2-XX	.080 2,03	.084 2,13	.045 1,14	1/16 1,59	(03) GOLD OR (04) ELECTRO-TIN
10-866-2-XX	.115 2,92	.084 2,13	.045 1,14	1/16 1,59	(03) GOLD OR (04) ELECTRO-TIN
10-867-11-XX	.154 3,91	.037 0,94	.026 0,66	1/64 0,40	(03) GOLD OR (04) ELECTRO-TIN
-1-XX	.154 3,91	.033 1,35	.031 0,79	1/32 0,79	(03) GOLD OR (04) ELECTRO-TIN
-2-XX	.154 3,91	.084 2,13	.045 1,14	1/16 1,59	(03) GOLD OR (04) ELECTRO-TIN
-3-XX	.154 3,91	.115 2,92	.045 1,14	3/32 2,38	(03) GOLD OR (04) ELECTRO-TIN
-4-XX	.154 3,91	.147 3,73	.045 1,14	1/8 3,18	(03) GOLD OR (04) ELECTRO-TIN
10-868-2-XX	.250 6,35	.084 2,13	.045 1,14	1/16 1,59	(03) GOLD OR (04) ELECTRO-TIN
10-869-4-XX	.281 7,14	.147 3,73	.045 1,14	1/8 3,18	(03) GOLD OR (04) ELECTRO-TIN
10-870-4-XX	.312 7,92	.147 3,73	.045 1,14	1/8 3,18	(03) GOLD OR (04) ELECTRO-TIN
10-871-2-XX	.344 8,74	.084 2,13	.045 1,14	1/16 1,59	(03) GOLD OR (04) ELECTRO-TIN
09-8190-2-04	.550 13,97	.084 2,13	.045 1,14	1/16 1,59	(04) ELECTRO-TIN
09-8148-1-03	.580 14,73	.053 1,35	.031 0,79	1/32 0,79	(03) GOLD
09-8002-1-04	1.000 25,40	.053 1,35	.031 0,79	1/32 0,79	(04) ELECTRO-TIN

10-8XX-X-XX P.C. PIN .025 09-80XX-X-XX

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.052 DIA (#55 DRILL)




PART NUMBER	H	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-875-1-05	.100 2,54	.051 1,30	1/32 0,79	(05) ELECTRO-SOLDER
-2-05	.100 2,54	.082 2,08	1/16 1,59	(05) ELECTRO-SOLDER
10-876-1-05	.200 5,08	.051 1,30	1/32 0,79	(05) ELECTRO-SOLDER
-2-05	.200 5,08	.082 2,08	1/16 1,59	(05) ELECTRO-SOLDER
09-8082-1-04	.500 12,7	.051 1,30	1/32 0,79	(04) ELECTRO-TIN
09-8081-1-05	.700 17,78	.051 1,30	1/32 0,79	(05) ELECTRO-SOLDER

09-8XXX-X-03 P.C. PIN .040

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.043 DIA (#57 DRILL)




PART NUMBER	H	L	K	P	BOARD THICKNESS	STANDARD (XX) FINISH
09-8154-1-03	.623 15,82	.051 1,30	.033 0,84	.045 1,14	1/32 0,79	(03) GOLD
09-8070-1-03	.684 17,37	.051 1,30	.035 0,89	.031 0,79	1/32 0,79	(03) GOLD
09-8155-1-03	.772 19,61	.051 1,30	.033 0,84	.045 1,14	1/32 0,79	(03) GOLD
09-8165-2-03	1.290 32,77	.085 2,16	.035 0,89	.031 0,79	1/16 1,59	(03) GOLD

10-850-X-01 P.C. PIN .040

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)




MATERIAL: BRASS

PART NUMBER	H	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-850-11-01	.224 5,69	.047 1,19	1/64 0,40	(01) SILVER
-1-01	.240 6,10	.063 1,60	1/32 0,79	(01) SILVER
-2-01	.270 6,86	.093 2,36	1/16 1,59	(01) SILVER
-3-01	.300 7,62	.123 3,12	3/32 2,38	(01) SILVER
-4-01	.330 8,38	.153 3,89	1/8 3,18	(01) SILVER

09-8XXX-X-XX P.C. PIN .040 10-8XX-X-XX

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.043 DIA (#57 DRILL)



PART NUMBER	H	L	P	BOARD THICKNESS	STANDARD (XX) FINISH
09-8075-1-03	.200 5,08	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.200 5,08	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8084-2-03	.250 6,35	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
10-891-1-03	.300 7,62	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.300 7,62	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8156-4-03	.300 7,62	.150 3,81	.045 1,14	1/8 3,18	(03) GOLD
09-8083-1-03	.400 10,16	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.400 10,16	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8157-1-03	.458 11,63	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
09-8059-1-03	.500 12,7	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.500 12,7	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8159-1-03	.570 13,97	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
10-892-1-03	.600 15,24	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.600 15,24	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8013-2-03	.625 15,88	.084 2,13	.040 1,02	1/16 1,59	(03) GOLD
09-8007-2-03	.650 16,51	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8158-2-03	.675 17,15	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8043-2-03	.690 17,53	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8076-1-03	.700 17,78	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.700 17,78	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8160-2-03	.710 18,03	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8067-1-03	.720 18,29	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.720 18,29	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8042-1-03	.740 18,80	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
09-8184-2-03	.750 19,05	.084 2,13	.040 1,02	1/16 1,59	(03) GOLD
09-8060-1-03	.800 20,32	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.800 20,32	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8185-2-03	.843 21,41	.084 2,13	.040 1,02	1/16 1,59	(03) GOLD
10-893-1-03	.900 22,86	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	.900 22,86	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
-3-03	.900 22,86	.113 2,87	.045 1,14	3/32 2,38	(03) GOLD
09-8161-2-03	1.000 25,4	.084 2,13	.040 1,02	1/16 1,59	(03) GOLD
09-8039-3	1.020 25,91	.113 2,87	.045 1,14	3/32 2,38	(03) GOLD
09-8061-1-03	1.060 26,82	.051 1,30	.045 1,14	1/32 0,79	(03) GOLD
-2-03	1.060 26,82	.082 2,08	.045 1,14	1/16 1,59	(03) GOLD
09-8162-2-03	1.088 27,64	.084 2,13	.040 1,02	1/16 1,59	(03) GOLD
09-8163-1-05	1.220 30,99	.051 1,30	.045 1,14	1/32 0,79	(05) ELECTRO-SOLDER

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY.

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161


**30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • 1-800-847-4162
FAX (212) 995-0161**

P.C. PINS

10-8XX-X-XX P.C. PIN .040, FEED THRU

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)




PART NUMBER	H	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-857-2-XX	.172 4.37	.094 2.39	1/16 1.59	
-3-XX	.172 4.37	.125 3.18	3/32 2.38	
-4-XX	.172 4.37	.156 3.96	1/8 3.18	(03) GOLD OR
10-858-3-XX	.313 7.96	.125 3.18	3/32 2.38	(04) ELECTRO-
-4-XX	.313 7.96	.156 3.96	1/8 3.18	TIN
10-859-2-XX	.345 8.76	.094 2.39	1/16 1.59	
10-860-2-XX	.407 10.34	.094 2.39	1/16 1.59	

10-820-X-01 P.C. PIN .040

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-820-1-01	.075 1.90	1/32 0.79	
-2-01	.105 2.67	1/16 1.59	(01) SILVER
-3-01	.135 3.43	3/32 2.38	
-4-01	.165 4.19	1/8 3.18	

10-80XX-X-03 P.C. PIN .040

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.043 ±.001 DIA (#57 DRILL)




PART NUMBER	H	L	K	BOARD THICKNESS	STANDARD (XX) FINISH
10-8021-1-03	.320 8.13	.051 1.30	.170 4.32	1/32 0.79	
-2-03	.320 8.13	.082 2.08	.170 4.32	1/16 1.59	(03) GOLD
-3-03	.320 8.13	.113 2.87	.170 4.32	3/32 2.38	
10-8022-1-03	.570 14.48	.051 1.30	.420 10.67	1/32 0.79	
-2-03	.570 14.48	.082 2.08	.420 10.67	1/16 1.59	(03) GOLD
-3-03	.570 14.48	.113 2.87	.420 10.67	3/32 2.38	

09-8003-1-03 P.C. PIN .080

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
09-8003-1-03	.105 2.67	1/16 1.59	(03) GOLD

10-8XX-X-04 P.C. PINS .040 FEED THRU

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.111 DIA (#34 DRILL)



* FOR -1 .071(1.80) BECOMES .063


MATERIAL: BRASS

PART NUMBER	H	L	A	BOARD THICKNESS	STANDARD (XX) FINISH
10-837-1-04	.188 4.78	.063 1.60	.219 5.56	1/32 0.79	
-2-04	.188 4.78	.094 2.39	.250 6.35	1/16 1.59	
-3-04	.188 4.78	.125 3.18	.281 7.14	3/32 2.38	(04) ELECTRO-
-4-04	.188 4.78	.156 3.96	.313 7.96	1/8 3.18	TIN
-6-04	.188 4.78	.219 5.56	.375 9.53	3/16 4.76	
-8-04	.188 4.78	.281 7.14	.438 11.13	1/4 6.35	
10-838-1-04	.375 9.53	.063 1.60	.219 5.56	1/32 0.79	
-2-04	.375 9.53	.094 2.39	.250 6.35	1/16 1.59	
-3-04	.375 9.53	.125 3.18	.281 7.14	3/32 2.38	(04) ELECTRO-
-4-04	.375 9.53	.156 3.96	.313 7.96	1/8 3.18	TIN
-6-04	.375 9.53	.219 5.56	.375 9.53	3/16 4.76	
-8-04	.375 9.53	.281 7.14	.438 11.13	1/4 6.35	
10-839-1-04	.375 9.53	.063 1.60	.406 10.31	1/32 0.79	
-2-04	.375 9.53	.094 2.39	.438 11.13	1/16 1.59	
-3-04	.375 9.53	.125 3.18	.469 11.91	3/32 2.38	(04) ELECTRO-
-4-04	.375 9.53	.156 3.96	.500 12.7	1/8 3.18	TIN
-6-04	.375 9.53	.219 5.56	.563 14.30	3/16 4.76	
-8-04	.375 9.53	.281 7.14	.625 15.87	1/4 6.35	

10-921-X-05 P.C. PINS .045

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.064 ±.002 DIA (#52 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-921-1-05	.062 1.57	1/32 0.79	
-2-05	.094 2.39	1/16 1.59	
-3-05	.125 3.18	3/32 2.38	(05) ELECTRO-SOLDER
-4-05	.156 3.96	1/8 3.18	

10-8009-X-XX P.C. PINS .062

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.067 ±.002 DIA (#51 DRILL)



PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-8009-1-XX	.053 1.35	1/32 0.79	(03) GOLD
-2-XX	.084 2.13	1/16 1.59	
-3-XX	.115 2.92	3/32 2.38	(04) ELECTRO-TIN

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY.

CONCORD
THE COMPONENT PEOPLE

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-8571 • TWX 710-581-4930
FAX (212) 995-0161


CONCORD
THE COMPONENT PEOPLE

P.C. PINS

09-8094-X-05 P.C. PIN .025

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.035 DIA (#65 DRILL)




PART NO. 09-8094-2-05
STANDARD (XX) FINISH (05) ELECTRO-SOLDER

MATERIAL: RED LEADED BRASS

10-922-X-05 P.C. PIN .045

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.064 ±.002 DIA (#52 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-922-1-05	.062 1.57	1/32 0.79	
-2-05	.094 2.39	1/16 1.59	(05) ELECTRO-SOLDER
-3-05	.125 3.18	3/32 2.38	
-4-05	.156 3.96	1/8 3.18	

MATERIAL: BRASS

14-986-2-03 P.C. PIN .050

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.035 DIA (#65 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
14-986-2-03	.094 2.39	1/16 1.59	(03) GOLD

MATERIAL: RED LEADED BRASS

10-901-X-05 P.C. PIN .060

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.064 DIA (#52 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-901-1-05	.062 1.57	1/32 0.79	
-2-05	.094 2.39	1/16 1.59	(05) ELECTRO-SOLDER
-3-05	.125 3.18	3/32 2.38	
-4-05	.156 3.96	1/8 3.18	

MATERIAL: BRASS

10-902-X-05 FOR .060 PINS

BASIC PART NO. FINISH

RECOMMENDED MOUNTING HOLE
.064 DIA (#52 DRILL)




PART NUMBER	L	BOARD THICKNESS	STANDARD (XX) FINISH
10-902-1-05	.062 1.57	1/32 0.79	
-2-05	.094 2.39	1/16 1.59	(05) ELECTRO-SOLDER
-3-05	.125 3.18	3/32 2.38	
-4-05	.156 3.96	1/8 3.18	

MATERIAL: BRASS

10-992-3-05 FOR .032 PIN

BASIC PART NO. FINISH




PART NUMBER	STANDARD (XX) FINISH	APPLICATION
10-992-3-05	(05) ELECTRO-SOLDER	FOR MOLDED ASSEMBLIES

MATERIAL: BRASS

10-924-1-XX P.C. PINS .025 FOR MOLDING

BASIC PART NO. FINISH




PART NUMBER	APPLICATION	STANDARD (XX) FINISH
10-924-1-XX	FOR MOLDED ASSEMBLIES	(03) GOLD OR (04) ELECTRO-TIN


MATERIAL: BRASS

10-8013-1-XX P.C. FLEXIBLE CABLE PIN .040

BASIC PART NO. FINISH



SUPPLIED UNASSEMBLED



PART NO. 10-8013-1-XX

STANDARD (XX) FINISH (03) GOLD OR (04) ELECTRO-TIN

TO BE ASSEMBLED AND SOLDERED ONTO FLAT FLEXIBLE CABLE