



MMS43



Active

Slide Switches



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Number of Positions = 3
- Four Pole - Three Throw Configuration (Pole-Throw)
- Actuator Style = Top
- Actuator Color = Black
- MMS Series

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Compare Products](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [ALCOSWITCH PRODUCTS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Number of Positions](#) = 3
- Configuration (Pole-Throw) = Four Pole - Three Throw
- Actuator Style = Top
- Mount Angle = Vertical
- Grade = Instrumentation
- Termination Type = PC

Electrical Characteristics:

- Contact Rating = 100mA @ 30 VDC

Body Related Features:

- Actuator Color = Black
- Series = MMS
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 2.50 [0.098]
- Actuator Length (mm [in]) = 2.01 [0.079]
- Actuator Material = Polyester

Contact Related Features:

- Contact Plating = Silver
- Contact Material = Copper Alloy

Configuration Related Features:

- Terminal Configuration = Standard
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240C, Wave solder capable to 260C, Wave solder capable to 265C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Alcoswitch