



Our commitment. Your advantage.

- [Products](#)
- [Documentation](#)
- [Resources](#)
- [My Account](#)
- [Customer Support](#)

[Home](#) > [Products](#) > [By Type](#) > [Resistors](#) > [Product Feature Selector](#) > Product Details

4295XF501 Product Details

[Live Product Chat](#)



4295XF501
(1623843-4)

TE Internal Number: 1623843-4

[Active](#)

Variable Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Variable Resistor
- Resistor Type = Trimmer
- Resistance Selection = <1K ?
- Resistance = 500 ?
- Power Rating = .50 W

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • Professional Trimmers - Type 4295 Series - Tyco Elec... (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
---	--

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Variable Resistor • Resistor Type = Trimmer • Resistance (?) = 500 • Element = Cermet • Sealed = Yes • Mount Angle = Vertical • Termination Type = PCB Terminations <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Resistance Selection (?) = <1K • Power Rating (W) = 0.50 • Tolerance (%) = 10 <p>Termination Related Features:</p> <ul style="list-style-type: none"> • Termination Post Orientation = 5.0 x 2.5 <p>Body Related Features:</p> <ul style="list-style-type: none"> • Series = 4295 • Package, Component Size = 10 	<p>Configuration Related Features:</p> <ul style="list-style-type: none"> • Sections = Single • Adjustment Location = Side • Adjustment Style = Finger Adjust • Operating Function = Single Turn <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Converted to comply with RoHS directive <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Temperature Coefficient (ppm/°C) = 100 <p>Other:</p> <ul style="list-style-type: none"> • Brand = Citec
--	---

[Provide Website Feedback](#) | [Need Help?](#)