


HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY

MT-LWA-.078-X-SP

MT-LWA

CM9832-000

TE Internal Number: CM9832-000

Always EU RoHS/ELV Compliant

Wall Type **Single**

Resistant To **Fluids, Impact, Radiation Sterilization, Strain**

Product Source **US**

Packaging Method **Cut Piece, Spool, Stick**

Shrink Ratio **2:1**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Wall Type	Single
	Product Family	MT-LWA
Electrical Characteristics	Voltage (Max) (kV)	1
Body Features	Shrink Ratio	2:1
	Color	Clear
	Flexibility	Flexible
	Material	Medical Grade Crosslinked Polyolefin
	Fluid Type	Medical Fluids, Water
Dimensions	Recovered Wall Thickness (Nominal)	.31 mm [.017 in]
	Recovered Inside Diameter (Max)	.66 mm [.026 in]
	Expanded Inside Diameter (Min)	1.98 mm [.078 in]
Usage Conditions	Resistant To	Fluids, Impact, Radiation Sterilization, Strain
	Recovery Temperature (°C)	110
	Operating Temperature Range (°C)	-40 – 110
	Flammability	Non-Flame-Retardant

Flammability

Heat Flame Resistance

Fluid Resistance

Moisture/Spray Protection, Splash Protection

Shrink Temperature (Min) (°C)

110

Product Availability

Applicable Region

Global

Packaging Features

Packaging Method

Cut Piece, Spool, Stick

Other

Product Source

US

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)