







- D
- NOTES:
1. TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15

2. FOR APPLICATION INFORMATION SEE AMP SPEC. 114-19019.

3. FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108-19064




PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.





LOC		DIST		REVISIONS			
H	—	P	LTR	DESCRIPTION	DATE	DMN	APRD
		J4		ECR-14-008810	12JUN14	CW	SH
		J5		ECO-15-014053	24SEP2015	AD	SH
		J6		ECO-16-004330	24MAR2016	AD	SH

216548




		800 PCS. ON A 60cm. DIA. REEL		6 POSITIONS/ 6 CONTACTS.		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL		HOUSING: PBT,UL 94V-HB COLOR: BLACK		216548-1	
PACKAGING		REMARKS		FINISH		SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		CONTACTS: PHOSPHOR BRONZE		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.											
DIMENSIONS: mm				TOLERANCES UNLESS OTHERWISE SPECIFIED:				DMN 22JAN92			
				0 PLG ± -				CHK C.STERKEN -			
				1 PLG ± -				NAME			
				2 PLG ± -				L.V.SOEST			
				3 PLG ± -				PRODUCT SPEC			
				4 PLG ± -				APPLICATION SPEC			
ANGLES ± -								WEIGHT -			
FINISH								A2			
MATERIAL								00779			
SEE TABLE				SEE TABLE				C216548			
CUSTOMER DRAWING								SCALE -			
								SHEET 1 OF 3			
								REV J6			

LOC		DIST		REVISIONS			
H		—		P	LTR	DATE	DWN
				DESCRIPTION			
				SEE SHEET 1/3			

- NOTES:
1. TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15
 2. FOR APPLICATION INFORMATION SEE AMP SPEC. 114–19019.
 3. FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108–19064



216548



PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.

A

B

C

D

A





B

C

D

800 PCS. ON A 60cm. DIA. REEL		6 POSITIONS/ 4 CONTACTS.	IN CONTACT AREA: 1.2 μ m MIN. SEL. GOLD OVER 1.2 μ m MIN. NICKEL	HOUSING: PBT, UL 94V–HB COLOR: BLACK	216548–2
PACKAGING	REMARKS	FINISH	SOLDER TINES: 2.0 μ m MIN. TIN OVER 1.2 μ m MIN. NICKEL	CONTACTS: PHOSPHOR BRONZE	
THIS DRAWING IS A CONTROLLED DOCUMENT.					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN J. V. LIEMPT	22JAN92	
0 PLG 1 PLG 2 PLG 3 PLG 4 PLG		$\pm$ $\pm$ $\pm$ $\pm$ $\pm$	CHK C. STERKEN	—	NAME
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APPRO L. V. SOEST	—	MODULAR JACK, 6 POS. TOP ENTRY, SMALL SIZE WITH PANEL STOPS, FOR PRINTED CIRCUIT BOARDS
MATERIAL		ANGLES	APPLICATION SPEC	—	SIZE
SEE TABLE		FINISH	WEIGHT	—	CAGE CODE
					DRAWING NO
					216548
					SCALE
					SHEET
					2 OF 3
					REV
					J6

- NOTES:
1. TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.15
 2. FOR APPLICATION INFORMATION SEE AMP SPEC. 114–19019.
 3. FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108–19064




216548

C

C

B

B



A

A

PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.05
PRINTED CIRCUIT BOARD THICKNESS: 1.6 mm NOMINAL.

LOC		DIST		REVISIONS			
H	—	P	LTR	DESCRIPTION		DATE	DWN
				SEE SHEET 1/3			APRO

240 PCS. IN ONE TRAY		6 POSITIONS/ 4 CONTACTS.		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		HOUSING: PBT,UL 94V-HB COLOR: BLACK CONTACTS: PHOSPHOR BRONZE		1-216548-5			
240 PCS. IN ONE TRAY		6 POSITIONS/ 4 CONTACTS.		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		HOUSING: PBT,UL 94V-VO COLOR: GRAY CONTACTS: PHOSPHOR BRONZE		216548-6			
800 PCS. ON A 60cm. DIA. REEL		6 POSITIONS/ 4 CONTACTS.		IN CONTACT AREA: 1.2µm MIN. SEL. GOLD OVER 1.2µm MIN. NICKEL SOLDER TINES: 2.0µm MIN. TIN OVER 1.2µm MIN. NICKEL		HOUSING: PBT,UL 94V-HB COLOR: BLACK CONTACTS: PHOSPHOR BRONZE		216548-5			
PACKAGING				REMARKS		FINISH		MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.											
DIMENSIONS: mm				TOLERANCES UNLESS OTHERWISE SPECIFIED:		TE Connectivity					
				0 PLG ± 1 PLG ± 2 PLG ± 3 PLG ± 4 PLG ± ANGLES ± FINISH ±							
DRAWING				CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL				SEE TABLE		WEIGHT		A2		00779	
SEE TABLE				SEE TABLE		—		G=216548		—	
CUSTOMER DRAWING				SCALE		—		SHEET		3 of 3	
								REV		J6	



TE Connectivity

MODULAR JACK, 6 POS. TOP ENTRY,
SMALL SIZE WITHOUT PANEL STOPS,
FOR PRINTED CIRCUIT BOARDS

SIZE A2
CAGE CODE 00779
DRAWING NO. 216548

SCALE

SHEET

3 of 3

REV J6