




## RNF-3000-9/3-8-SP Product Details

[Share](#) | [Print](#) | [Email](#)


**RNF-3000-9/3-8-SP**

TE Internal Number: 2376334004

 Active

### Heat Shrink Tubing

 Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Heat Shrinkable Tubing
- Product Name = RNF-3000
- Product Source = U.K., U.S.
- Flexible
- Thin Wall Style

[View all Features](#)

#### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Heat Shrinkable Tubing
- Color = Gray

#### Dimensions:

- Expanded ID, Min. (mm [in]) = 9.00 [0.354]
- Recovered ID, Max. (mm [in]) = 3.00 [0.118]

#### Body Features:

- Product Name = RNF-3000
- Pliancy = Flexible
- Wall Style = Thin
- Wall Type = Single
- Material = Crosslinked Polyolefin
- Shrink Ratio = 3:1
- Fluid Type = Brake Fluid, Chemicals/Solvents, Water
- Resistant To = Abrasion, Fluids, Mechanical Damage, Strain
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.75 [0.0295]

#### Housing Features:

- Material Systems = No

#### Industry Standards:

- Government/Industry Qualification = No
- Flammability Rating Type = Flame-Retardant
- UL Rating = Recognized
- CSA Certified = Yes
- Approved Standards = BS 4G 198 Part 3 Type 11B, CSA LR31929, DEF Std 59-97 Type 2B, UL E35586, VDE 0341 Part 9005 Type A&B, VG95343 Part 5 Type A
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Environmental:

- Fluid Resistance = Splash Protection
- Operating Temperature (°C) = -55 - +135

#### Conditions for Usage:

- Full Recovery Temperature (°C) = 120
- Shrink Temperature, Min. (°C) = 80
- High Temperature Compatible = No

#### Operation/Application:

- Application = Cable Jacket Repair Sleeve, Cable Jacketing, Color Coding, Identification, Insulation and Protection, Wire Bundling
- Emission Free = No
- Product Use = Cables, Electronic Components, Harnesses, Wire Terminations

#### Packaging Features:

- Packaging Method = Spool

#### Product Availability:

- Product Source = U.K., U.S.

#### Other:

- Brand = Raychem

#### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

#### Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

