



HARNESSING

BREAKOUTS/TRANSITIONS



✓ Active

TE CONNECTIVITY (TE)

322A514-4-0

Raychem

322A514-4-0

TE Internal Number: 823171-000

Alias ID: 3-1196422-6

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Molded Part Shape 90° Side-Breakout, One to Two Cables, T Shape

Wire/Cable OD (mm) 18, 20, 22

Wire/Cable OD (in) .71, .79, .87

Wire/Cable Main Branch OD (mm) 10, 11, 12

Wire/Cable Sm Branch OD (mm) 10, 11, 12

Wire/Cable Sm Branch OD (in) .39, .43, .47

Operating Temperature Range -55 – 135 °C [-67 – 275 °F]

[↓ PRODUCT DRAWING](#)

English

DOCUMENTATION

Product Drawings

Transition, 90 Degrees Side Breakout, Thinwall

PDF

English

Product Environmental Compliance

Safety Data Sheet

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

EPS Heat Shrinkable Polymeric Products

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Shape 90° Side-Breakout, One to Two Cables, T Shape

Product Type Molded Part

Molded Part Type Breakouts/Transitions

Body Features

Material Systems Code 10

Adhesive Pre-Coat No

Color Black

Usage Conditions

Operating Temperature Range -55 – 135 °C [-67 – 275 °F]

Other

Wire/Cable OD (mm) 18, 20, 22

Wire/Cable OD (in) .71, .79, .87

Wire/Cable Main Branch OD (mm) 10, 11, 12

Wire/Cable Sm Branch OD (mm) 10, 11, 12

Wire/Cable Sm Branch OD (in) .39, .43, .47

Fluid/Chemical Resistance Occasional exposure to fluids

Special Requirements Flame Retarded

Adhesive Type Adhesive Purchased Separately

Statement of Compliance

Statement of Compliance

PDF