




Wire Protection & Management > Heat Shrink Shapes > Cable Transitions & Breakouts



Adhesive Requirement: **Adhesive Precoat**

Operating Temperature Range: **-20 – 60 °C [-4 – 140 °F]**

Fluid & Chemical Resistance: **Occasional Fluid Exposure**

Adhesive Options: **/42 Precoat**

Features

Configuration Features

Adhesive Requirement	Adhesive Precoat
----------------------	------------------

Body Features

Material	Polyolefin Flexible Modified
----------	------------------------------

Dimensions

Inside Diameter Range (Body)	24 – 57 mm [.94 – 2.24 in]
Inside Diameter Range (Leg 1)	12 – 57 mm [.47 – 2.24 in]

Usage Conditions

Operating Temperature Range	-20 – 60 °C [-4 – 140 °F]
-----------------------------	---------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----

Other

Fluid & Chemical Resistance	Occasional Fluid Exposure
Adhesive Options	/42 Precoat

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Documents

Product Drawings

[QFT3-130/42-0](#)

English

Datasheets & Catalog Pages

[Raychem Molded Parts Visual Guide](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

English



[Safety Datasheet](#)

French

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English