

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1718573002](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: 2.54mm Pitch, KK 254 RPC Wire-to-Board Right-Angle Header with Friction Lock, Tin (Sn) Plating, Tape and Reel, 2 Circuits

Documents:

Drawing (PDF)	Product Specification PS-171856-0002-001 (PDF)
3D Model	Packaging Specification PK-171857-0001-001 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-171857-0002-001 (PDF)
Product Specification PS-171856-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)



Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	171857
Application	Power, Signal, Wire-to-Board
Overview	KK Interconnect Systems
Product Name	KK 254
Taxonomy	PCB Headers and Receptacles
UPC	887191716190

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-1
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	0.250/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Plating min - Mating	1.524µm
Polarized to Mating Part	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact 4.0A

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[171857 Series](#)

Mates With

[4455](#) , [2695](#) , [6471](#)

Voltage - Maximum 500V

Solder Process Data

Duration at Max. Process Temperature (seconds) 030

Lead-free Process Capability SMC&WAVE

Max. Cycles at Max. Process Temperature 003

Process Temperature max. C 260

Material Info

Cross-Plant Material Status LT

Reference - Drawing Numbers

Packaging Specification PK-171857-0001-001

Product Specification PS-171856-0001-001, PS-171856-0002-001

Sales Drawing SD-171857-0001-000, SD-171857-0001-002

Symbol/Footprint Data SYM-171857-0002-001

This document was generated on 10/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION