




Connectors > Automotive Connectors > Seals & Cavity Plugs



Connector Seal Type: **Cavity Blanking Plug**

Operating Temperature (Max): 65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C [149 °F, 158 °F, 167 °F, 176 °F, 185 °F, 194 °F, 212 °F, 221 °F, 230 °F, 248 °F, 257 °F, 266 °F]

Primary Product Color: **Black**

Operating Temperature Range: -40 – 130 °C [-40 – 266 °F]

Features

Product Type Features

| | |
|---------------------|----------------------|
| Connector Seal Type | Cavity Blanking Plug |
|---------------------|----------------------|

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Usage Conditions

| | |
|-----------------------------|---|
| Operating Temperature (Max) | 65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C [149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F] |
| Operating Temperature Range | -40 – 130 °C[-40 – 266 °F] |

Packaging Features

| | |
|--------------------|--------|
| Packaging Quantity | 5000 |
| Packaging Method | Carton |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) |

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-T4827-CH8172
TIMER, CONNECTOR HOUSING




TE Part # 953756-1
47W RCPT HSG ASSY




TE Part # 1-1379208-1
26W ASSY RECEPTACLE HSG




TE Part # 1379208-3
26W ASSY RECEPTACLE HSG



TE Part # 1379208-4
26W ASSY RECEPTACLE HSG



TE Part # 953756-7
47W RCPT HSG ASSY



TE Part # 953756-9
47W RCPT HSG ASSY

Documents

Product Drawings
CAVITY PLUG

English

CAD Files
Customer View Model



[ENG_CVM_100132-1_A3.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_100132-1_A3.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_100132-1_A3.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

French

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

French