

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2043160006](#)  
**Status:** **Active**  
**Overview:** [Sentrality Pin and Socket Interconnect System](#)  
**Description:** [Sentrality 6.00mm Top-entry, Knurled Press-fit Socket Assembly in Tray](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2043180006-PK-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 2043130006-TS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 2043131234-TS-000 (PDF)</a>
<a href="#">Product Specification 2043130006-PS-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification 2043130006-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



*Series image - Reference only*

**General**

Product Family	PCB Receptacles
Series	<a href="#">204316</a>
Application	Busbar-to-Board, Busbar-to-Busbar, Power
Comments	Current and voltage performances are dependent upon application variables.
Overview	<a href="#">Sentrality Pin and Socket Interconnect System</a>
Product Name	Sentrality
Taxonomy	PCB Headers and Receptacles
UPC	191130149919

**Physical**

Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	6.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	4.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Top-entry
Net Weight	6.521/g
Number of Rows	1
Orientation	Vertical
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	N/A
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Press-Fit

**Electrical**

Current - Maximum per Contact	140.0A
Voltage - Maximum	600V

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2043130006-AS-000
Packaging Specification	2043180006-PK-000
Product Specification	2043130006-PS-000
Sales Drawing	2043160006-SD-000
Test Summary	2043130006-TS-000, 2043131234-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[204316 Series](#)

**Mates With**

6.00mm Male Pin [203263](#)

This document was generated on 10/31/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**