

Product Details for 228217 - 1

No Image Available

228217 - 1

 [Active](#)

SMB RF Connectors

[Not ELV or RoHS Compliant](#) (Find RoHS Compliant Alternates)

Product Highlights:

- ? Connector
- ? Jack
- ? Standard
- ? Terminate To Coaxial Cable
- ? Coupler Style = Quick Connect/Disconnect

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [JACK, BULKHEAD, SERIES SMB](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Connector, Coaxial, SMB Series, Commercial](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [Coaxial RF Series 50 -Ohm Commercial SMB Bulkhead Jac...](#) (PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Jack
- ? Connector Series = Standard
- ? [Body Style](#) = Straight
- ? [Grade](#) = Commercial
- ? Dielectric Material = PTFE

Mechanical Attachment:

- ? [Panel Attachment](#) = With
- ? [Panel Attachment Style](#) = Front Mount
- ? Panel Attachment Method = Bulkhead

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 50
- ? Environmental Seal = Without

Termination Related Features:

- ? [Coaxial Cable Termination Type](#) = Crimp

Body Related Features:

- ? Coupler Style = Quick Connect/Disconnect
- ? [Pin Protection](#) = Without
- ? Solder Lug = Without
- ? [Body Plating](#) = Nickel Over Copper

Contact Related Features:

- ? [Center Contact Plating](#) = Gold
- ? Contacts = With

Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 174, 188, 316

Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable

Other:

- ? Brand = AMP