

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0387206305

Status:

Active

Overview:

Beau™ Barrier Strips

Description:

9.53mm Pitch Beau™ PCB Terminal Strip, without Mounting Ends, 5 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-38710-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

38720

N/A

One Piece

Beau™ Barrier Strips

Fixed Mount Barrier

Barrier Strip

800756334295

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Entry Angle

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length

PCB Retention

PCB Thickness - Recommended

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

5

5

Black

Horizontal

None

Brass

Tin

Tin

Polyester

1

Horizontal

4.80mm

None

3.18mm

No

9.53mm

9.53mm

3.810µm

3.810µm

No

Dual-Barrier

No

No

-40°C to +130°C

14, 16, 18, 20, 22

0.50-1.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

15.0A

300V

Solder Process Data

Lead-freeProcess Capability


WAVE

Material Info

Engineering Number

72505-C

Reference - Drawing Numbers



EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/30/2017 (7 July

2017)

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

38720 Series

This document was generated on 07/18/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION