


557566-1 Product Details

 [Live Product Chat](#)



557566-1

TE Part Number: 557566-1

 **Superseded**

[Add to Part List](#)
[Search for Replacement Parts](#)

PCB Mounted Jacks - Single Port, Multi-port and Stacked

 [5 of 6 EU RoHS/ELV Compliant](#) ([Find RoHS Compliant Alternates/Statement of Compliance](#))

Product Highlights:

- Jack
- Multiple Port Configuration
- 1 x 8 Jack Configuration
- Jack Type = RJ45
- Number of Positions = 8

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Eight Position Multiple Port Right Angle Modular Jacks](#) (PDF, English)
- [High Performance Modular Plugs & Jacks, PCB Mounted](#) (PDF, English)

Application Specifications:

- [Modular Jacks](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Jack
- [Jack Type](#) = RJ45
- [Number of Positions](#) = 8
- [PCB Mount Angle](#) = Side Entry (Right Angle)
- [PCB Mount Style](#) = Thru Hole
- [PCB Termination Type](#) = Solder
- [Shielded](#) = No
- [Performance Category](#) = Cat 4
- Number of Contacts Loaded = 8
- Grounding Options = Without
- [Panel Stops](#) = Without
- [Keyed](#) = No
- [Profile](#) = Standard
- [Color](#) = Black
- Comment = On any modular jack, Terminal No. 1 is the terminal to the extreme left as you face the jack opening, tab notch down.

Mechanical Attachment:

- [Jack Configuration](#) = 1 x 8
- [Panel Attachment](#) = Without

Termination Related Features:

- [Solder Tail Contact Plating](#) = Tin-Lead over Nickel

Body Related Features:

- Port Configuration = Multiple
- [Inverted Jack Face](#) = No
- [LED](#) = Without
- [PCB Tail Length \(mm \[in\]\)](#) = 3.56 [0.140]
- Number of Contacts Loaded, RJ45 (8 Positions) = 8

Contact Related Features:

- [Contact Mating Area Plating Material](#) = Gold (50) over Nickel (50)
- Contact Material = Phosphor Bronze

Housing Related Features:

- Housing Material = High Temperature Nylon
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C

Packaging Related Features:

- Packaging Method = Tray
- Packaging Quantity = 10

Other:

- Brand = AMP