



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	David Benfer	<b>Contact Title</b>	Product Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2014-10-10	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	6766638-1	<b>Amount</b>	48834.808	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirements by application of the selected exemption(s) - true								
<b>ChinaRoHS-0508</b>	Product(s) requires marking for the presence of restricted substances and must be marked with an Environmental Protection Use Period under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>EUREACH-1213</b>	Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH - Not Available / Not Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	1648800-1				1.0	6790.0	mg	
Material	2	PPA-GF33				1.0	6790.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.5	1.0	101.85	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	4.0	1.0	271.6	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	1.0	2240.7	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	67.9	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	23.0	1.0	1561.7	mg	
Substance	3	1,3-Benzenedicarb oxlyic acid, polymer with 1,4-benzenedicarb oxlyic acid, 1,6-hexanediamine and hexanedioic acid	Supplier	27135-32-6	37.5	1.0	2546.25	mg	
Sub-Item	1	1766100-1				24.0	824.367	mg	
Material	2	Beryllium Copper				24.0	47.7	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	24.0	0.00477	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	24.0	0.2862	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	24.0	4.77E-4	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	24.0	0.954	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	24.0	0.00954	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	24.0	0.2862	mg	
Substance	3	Copper	Supplier	7440-50-8	96.0485	24.0	45.81513	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	24.0	0.00477	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.6	24.0	0.2862	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	24.0	0.00477	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	24.0	2.385E-4	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	24.0	0.0477	mg	
Material	2	Phos Bronze				24.0	775.47	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	24.0	722.22235	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	24.0	0.15509	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	24.0	2.32641	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	24.0	0.077547	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	24.0	2.71415	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	24.0	0.11632	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	24.0	0.77547	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	24.0	0.0077547	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	24.0	0.77547	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	24.0	0.077547	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	24.0	44.97726	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	24.0	0.00387735	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	24.0	0.077547	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	24.0	0.38774	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	24.0	0.77547	mg	
Material	2	Gold Plate				24.0	0.095	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	24.0	0.094715	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	24.0	2.85E-4	mg	
Material	2	Tin Plate				24.0	0.049	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	24.0	4.8951E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	24.0	0.04895105	mg	
Material	2	Nickel Plate				24.0	1.053	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	24.0	0.002106	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	24.0	0.001053	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	24.0	1.04984	mg	
Sub-Item	1	1648799-1				7.0	1340.0	mg	
Material	2	PPA-GF33				7.0	1340.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.5	7.0	20.1	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	4.0	7.0	53.6	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	7.0	442.2	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	7.0	13.4	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	23.0	7.0	308.2	mg	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, 1,6-hexanediamine and hexanedioic acid	Supplier	27135-32-6	37.5	7.0	502.5	mg	
Sub-Item	1	1650591-1				2.0	6440.0	mg	
Material	2	Brass				2.0	3580.0	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.0358	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.358	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	3.58	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.358	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.716	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.0358	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	2.0	12.53	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	2.0	1172.3605	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	2.0	2255.4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.0179	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	2.0	132.46	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.358	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	1.79	mg	
Material	2	PPA-GF33				2.0	2860.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.5	2.0	42.9	mg	
Substance	3	Antimonate (SbO3 <sup>1-</sup> ), sodium (1:1)	Supplier	15432-85-6	4.0	2.0	114.4	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	2.0	943.8	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	28.6	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	23.0	2.0	657.8	mg	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, 1,6-hexanediamine and hexanedioic acid	Supplier	27135-32-6	37.5	2.0	1072.5	mg	