




Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Shrouds



Connector Mounting Accessory Type: **Coupling Shroud**

Mating Alignment: **With**

Number of Positions: **12**

Number of Rows: **2**

Number of Columns: **6**

Features

Product Type Features

Connector Mounting Accessory Type	Coupling Shroud
Sealable	No

Configuration Features

Number of Positions	12
Number of Rows	2
Number of Columns	6

Electrical Characteristics

Termination Resistance	15 mΩ
Dielectric Withstanding Voltage (Max)	600 V
Insulation Resistance	5000 MΩ

Body Features

Shroud Material	Thermoplastic
Shroud Color	Black

Contact Features

CompactPCI	No
------------	----

Mechanical Attachment

Mating Alignment Type	Latched
PCB Mount Retention	Without



Mating Alignment	With
------------------	------

Dimensions

Product Length	19.94 mm[.78 in]
Product Height	11.76 mm[.46 in]
Product Width	18.67 mm[.735 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	Insert Receptacle Assembly w/Guide Ribs (only) into shroud.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5-103969-1 10X2 MTE RCPT SR RIBBED .100CL	 TE Part # 5-103969-3 5X4 MTE RCPT SR RIBBED .100CL	 TE Part # 5-103969-4 4X5 MTE RCPT SR RIBBED .100CL	 TE Part # 5-103969-2 8X3 MTE RCPT SR RIBBED .100CL
--	--	---	---

Also in the Series | AMPMODU MTE

 Insertion & Extraction Tools(2)	 PCB Connector Shrouds(40)	 PCB Headers & Receptacles(763)	 Ribbon Connector Accessories(1)
 Standard Rectangular Connectors(2)	 Wire-to-Board Connector Assemblies & Housings(585)	 Wire-to-Board Connector Contacts(32)	

Documents

Product Drawings
12 MTE COUPLING SHRD DR
English

CAD Files
Customer View Model
ENG_CVM_CVM_103681-3_P.2d_dxf.zip
English
3D PDF
3D
Customer View Model



[ENG_CVM_CVM_103681-3_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_103681-3_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP MODU MTE Section of Catalog 1307819](#)

English

[AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT](#)

English

[AMPMODU MTE INTERCONNECT SYSTEM](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English