

250 FAST FLG RCPT HSG NAT V2 GWT ✓ ACTIVE

TE Part # 1969507-4

TE Internal #: 1969507-4

[View on TE.com >](#)



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Receptacle**

Housing Type: **Receptacle Housing**

Number of Positions: **1**

Terminal Orientation: **Flag**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Housing Type	Receptacle Housing
Sealable	No
Insulated	No

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Housing Color	Natural
Mating Retention	With
Mating Alignment	With

Contact Features

Terminal & Splice Type	Receptacle
Terminal Orientation	Flag

Mechanical Attachment



Mounting Style	Free Hanging
----------------	--------------

Housing Features

Housing Material	Nylon
------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	欧洲化学品管理局最新发布的SvHCs候选清单: 2019年1月 (197) SvHCs候选清单的声明更新至: 2019年1月 (197)
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought




TE Part #2005249-9
PDL 2P CAP 3.96 P/M
(GWT) BLK




TE Part #1803006-8
CRIMPER, WIRE F



TE Part #1803615-7
ANVIL, COMBINATION,
END FEED



TE Part #1969453-6
HSG, RECP, POSI-
LOCK&STD FAST250



TE Part #1969507-9
HOUSING, RECEPTACLE,
FLAG FASTON, CLOSE



TE Part #2-1803059-7
ANVIL COMBINATION,
END FEED



TE Part #2321920-3
PERIMETER SEAL PLUG
HOUSING 3PIN



TE Part #2321922-3
REAR WIRE SEAL 3PIN



TE Part #2321922-4
REAR WIRE SEAL 4PIN

Documents

Product Drawings

250 FAST FLG RCPT HSG NAT V2 GWT

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1969507-4_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1969507-4_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1969507-4_B.3d_stp.zip](#)

English

Product Environmental Compliance

[MD_1969507-4_060620181332_dmtec](#)



English

[MD_1969507-4_060620181332_dmtec](#)

English