




TE Internal #: 1057463-1

Between Series Adapters, Side A Interface OSM, Side A Gender Jack, Side B Interface OSN, Side B Gender Jack, Wire-to-Wire, Wire & Cable

[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Adapters > Between Series Adapters



Side A Interface: **OSM**

Side A Gender: **Jack**

Side B Interface: **OSN**

Side B Gender: **Jack**

Connector System: **Wire-to-Wire**

Features

Product Type Features

Side A Interface	OSM
Side A Gender	Jack
Side B Interface	OSN
Side B Gender	Jack
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Material	Stainless Steel
---------------	-----------------

Contact Features



RF Connector Center Contact Plating Material	Gold
--	------

RF Connector Center Contact Material	Brass
--------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	15 GHz
---------------------	--------

Circuit Application	Power & Signal
---------------------	----------------

Other

Gasket Material	Silicone Rubber
-----------------	-----------------

Dielectric Material	TFE Fluorocarbon
---------------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JUNE 2022 (224)</p> <p>Candidate List Declared Against: JUL 2021 (219)</p> <p>SVHC > Threshold:</p> <p>Pb (.6% in Component Part)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
--	---

Halogen Content	Not Yet Reviewed for halogen content
-----------------	--------------------------------------

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1-2016655-0 SMA, MALE-MALE, 18G, L1000, WITHOUT ARMOR</p>	 <p>TE Part # 1-2016657-0 N M DOUBLE, 18G, 1.0M WITHOUT ARMOR</p>	 <p>TE Part # 1-2016658-0 N M DOUBLE, 18G, 1.0M WITH ARMOR, PUR</p>	 <p>TE Part # 1-2016662-0 2.92M, BOTH END, WITH ARMOR CABLE, 40GHZ</p>
 <p>TE Part # 1-2016663-0 3.5 M DOUBLE, 26.5G, 1.0M, WITH ARMOR, BRAID</p>	 <p>TE Part # 5225392-7 SERIES N PLUG</p>	 <p>TE Part # 225392-2 SERIES N PLUG W/PROOF</p>	 <p>TE Part # 1-2016655-5 SMA M DOUBLE, 18G, 1.5M WITHOUT ARMOR</p>
 <p>TE Part # 1-2016656-5 SMA M DOUBLE, 18G, 1.5M WITH ARMOR, PUR</p>	 <p>TE Part # 1-2016657-5 N M DOUBLE, 18G, 1.5M WITHOUT ARMOR</p>	 <p>TE Part # 1-2016658-5 N M DOUBLE, 18G, 1.5M WITH ARMOR, PUR</p>	 <p>TE Part # 1-2016663-5 3.5 M DOUBLE, 26.5G, 1.5M, WITH ARMOR, BRAID</p>
 <p>TE Part # 2016655-6 SMA M DOUBLE, 18G, 0.6M WITHOUT ARMOR</p>	 <p>TE Part # 2016656-6 SMA M DOUBLE, 18G, 0.6M WITH ARMOR, PUR</p>	 <p>TE Part # 2016657-6 N M DOUBLE, 18G, 0.6M WITHOUT ARMOR</p>	 <p>TE Part # 2016658-6 N M DOUBLE, 18G, 0.6M WITH ARMOR, PUR</p>



Documents

Product Drawings

[3084 2240 00](#)

English

CAD Files

Customer View Model

[ENG_CVM_1057463-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1057463-1_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1057463-1_B.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RF Between Series Adapters](#)

English