



**AMP SSMA**

TE Internal #: 1045369-1

RF Connectors, SSMA RF Interface, Plug, 50 Ω, RG 405 Semi-Rigid, Threaded, 40 GHz Operating Frequency, 1 Position, Sealable, Wire & Cable, AMP SSMA

[View on TE.com >](#)

Connectors > RF Coax Connectors > RF Connectors



RF Interface: **SSMA**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **7.24 mm [ .285 in ]**

Impedance: **50 Ω**

Compatible With RF Cable Type: **RG 405 Semi-Rigid**

**Features**

**Product Type Features**

Connector Product Type	Housing
Connector Seal Type	Interfacial Seal
RF Interface	SSMA
RF Connector Style	Plug
Compatible With RF Cable Type	RG 405 Semi-Rigid
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Number of Positions	1
Number of Coaxial Contacts	1

**Electrical Characteristics**

Impedance	50 Ω
-----------	------

**Body Features**

Cable Connector Orientation	Straight
Body Material	Stainless Steel
Body Material Finish	Plated
Body Plating Material	Gold

**Termination Features**



Termination Method to Wire & Cable	Solder
------------------------------------	--------

### Mechanical Attachment

RF Connector Coupling Mechanism	Threaded
Connector Mounting Type	Cable Mount (Free-Hanging)

### Dimensions

RF Connector Mated Outer Diameter (Approximate)	7.24 mm [.285 in]
---	-------------------

### Usage Conditions

Operating Temperature Range	-65 – 165 °C [-85 – 329 °F]
-----------------------------	-----------------------------

### Operation/Application

Operating Frequency	40 GHz
---------------------	--------

### Packaging Features

Packaging Method	Package
------------------	---------

### Other

Coupling Nut Base Material	Stainless Steel
----------------------------	-----------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



## Also in the Series | AMP SSMA



## Documents

### Product Drawings

[SSMA CABLE PLUG 1001 7985 00](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_1045369-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1045369-1\\_A.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1045369-1\\_A.2d\\_dxf.zip](#)

English



### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

Products for Aerospace and Defense

English

### Instruction Sheets

Instruction Sheet (U.S.)

English