

1393230-9 ✓ ACTIVE

SCHRACK

TE Internal #: 1393230-9

Power Relays, Standard, Monostable, DC, 500 mW Coil Power Rating DC, 270 Ω Coil Resistance, 12 VDC Coil Voltage, 1 Form A (NO), AgSnO Contact Material

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Standard**

Coil Magnetic System: **Monostable, DC**

Coil Power Rating Class: **500 – 1000 mW**

Coil Power Rating DC: **500 mW**

Coil Resistance: **270 Ω**

Features

Product Type Features

Power Relay Type	Standard
------------------	----------

Electrical Characteristics

Coil Magnetic System	Monostable, DC
Coil Power Rating Class	500 – 1000 mW
Coil Power Rating DC	500 mW
Coil Resistance	270 Ω
Coil Voltage Rating	12 VDC
Contact Switching Voltage (Max)	400 VAC
Contact Voltage Rating	250 VAC

Body Features

Product Weight	18 g[.035 oz]
----------------	---------------

Contact Features

Contact Arrangement	1 Form A (NO)
Contact Current Class	10 – 20 A
Contact Current Rating (Max)	16 A
Contact Material	AgSnO
Contact Number of Poles	1
Relay Terminal Type	PCB-THT



Mechanical Attachment

Relay Mounting Type	Printed Circuit Board
---------------------	-----------------------

Packaging Features

Packaging Method	Box & Tube, Tube
------------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1393230-1
RP3SL024



TE Part # 1393230-5
RP3SLF12



TE Part # 1393230-3
RP3SLA12



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1393230-9_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393230-9_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393230-9_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Special Load PCB Relay RP3SL

English

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English

Agency Approvals

VDE Certificate

English