

1056740-1 ✓ ACTIVE

AMP | AMP SMP


TE Internal #: 1056740-1

RF Connector Shrouds, 2-Hole Flange Shroud Type, Shroud Diameter 12.19 mm [.48 in], High Force Applied Pressure, -55 – 105 °C [-67 – 221 °F], AMP SMP

[View on TE.com >](#)



Connectors > RF Coax Connectors > RF Coax Accessories > RF Connector Shrouds



Shroud Type: **2-Hole Flange**
Shroud Diameter: **12.19 mm [.48 in]**
Applied Pressure: **High Force**
Centerline (Pitch): **4.16 mm [.164 in]**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Applied Pressure	High Force
------------------	------------

Body Features

Shroud Material	Stainless Steel
Shroud Type	2-Hole Flange

Housing Features

Centerline (Pitch)	4.16 mm [.164 in]
--------------------	-------------------

Dimensions

RF Contact Spacing	4.32 mm [.17 in]
Shroud Diameter	12.19 mm [.48 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JUNE 2022 (224)
 Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | AMP SMP



Between Series Adapters(1)



In-Series Adapters(1)



RF Connector Shrouds(3)



RF Connectors(7)

Documents

Product Drawings

HOUSING, SHROUD, FULL DETENT, SMP, PASS

English

CAD Files

Customer View Model

[ENG_CVM_1056740-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1056740-1_D.3d_stp.zip](#)

English

Customer View Model



[ENG_CVM_1056740-1_D.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Datasheets & Catalog Pages](#)

[Products for Aerospace and Defense](#)

English