

1060985-1 ✓ ACTIVE

TE Internal #: 1060985-1

RF Connectors, MCX RF Interface, Jack, 50 Ω , Snap-On, 6 GHz

Operating Frequency, Cable-to-Cable, 1 Position, Printed Circuit Board, Board Mount

[View on TE.com >](#)



Connectors > RF Coax Connectors > RF Connectors > MCX Connector: Jack, Vertical, 50 Ohm



RF Interface: **MCX**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **3.48 mm [.137 in]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Snap-On**

[All MCX Connector: Jack, Vertical, 50 Ohm \(7\)](#)

Features

Product Type Features

Connector Shape	Circular
RF Interface	MCX
RF Connector Style	Jack
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	-------------

Body Features



Body Material	Brass
Body Material Finish	Plated
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Underplating Material	Copper, Nickel
	1397 μ m
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Beryllium Copper

Termination Features

Termination Post & Tail Length	2.92 mm[.115 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Retention	Without
RF Connector Coupling Mechanism	Snap-On
Connector Mounting Type	Board Mount
Detent	Without

Dimensions

Profile Height from PCB	5.36 mm[.211 in]
RF Connector Mated Outer Diameter (Approximate)	3.48 mm[.137 in]

Usage Conditions

Operating Temperature Range	-65 – 165 $^{\circ}$ C[-85 – 329 $^{\circ}$ F]
-----------------------------	--

Operation/Application

Operating Frequency	6 GHz
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Dielectric Material	TFE Fluorocarbon
---------------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------



EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

SVHC > Threshold:

Pb (3.7% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1362991-1
9637 7179 10,75 OHM OSX



TE Part # 1060787-1
5807 7985 09,OSX R/A CABL PLUG



TE Part # 1060960-1
5858 0000 10



TE Part # 2118308-6
4G WORLD BAND, METASPAN, PCB ANT, 190 MM

Documents

Product Drawings

[5862 5002 10,OSX JACK RECPT](#)

English

CAD Files

Customer View Model

[ENG_CVM_1060985-1_A.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_1060985-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1060985-1_A.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MCX Connectors](#)

English

[1-1773725-8_RF_COAX_QRG](#)

English