




Connectors > Rectangular Connectors > Rectangular Contact Inserts



Contact Insert Pole Configuration: 12+2

Number of Positions: 12

Features

Product Type Features

Product Type	Insert
Product Size	6

Configuration Features

Number of Positions	12
---------------------	----

Electrical Characteristics

Power Circuit Voltage	250 V
Power Circuit Current	10 A

Body Features

Material	PBT GF30
Color	Gray

Contact Features

Contact Insert Pole Configuration	12+2
-----------------------------------	------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	5

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Documents

CAD Files
3D PDF

3D

Customer View Model
[ENG_CVM_CVM_1103154-1_B_c-1103154-1-b.2d_dxf.zip](#)
English

Customer View Model
[ENG_CVM_CVM_1103154-1_B_c-1103154-1-b.3d_igs.zip](#)
English

Customer View Model
[ENG_CVM_CVM_1103154-1_B_c-1103154-1-b.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.