

1123343-1 ✓ ACTIVE

AMP | TH/.025 Connector System


TE Internal #: 1123343-1

Automotive Terminals, Receptacle, Mating Tab Width .025 in [.64 mm], Tab Thickness .025 in [.64 mm], 24 – 20 AWG Wire Size, TH/.025 Connector System

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > TH/.025 CONNECTOR SYSTEM, RECPT AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **.64 mm [.025 in]**

Mating Tab Thickness: **.64 mm [.025 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **24 – 20 AWG**

[All TH/.025 CONNECTOR SYSTEM, RECPT AND TAB \(26\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	.64mm
Contact Fabrication	Stamped & Formed
Typical Current Rating	4 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	.64 mm[.025 in]
Mating Tab Thickness	.64 mm[.025 in]
Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions



Wire Size	.22 – .56 mm ²
Wire Size Search	20 AWG, 21 AWG, 22 AWG, 23 AWG, 24 AWG
Wire Insulation Diameter	.95 – 1.72 mm [.037 – .067 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C [176 °F] [185 °F] [194 °F] [212 °F] [221 °F] [230 °F] [248 °F]
Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
Packaging Quantity	10000

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent

chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part # CAT-SIGH262
SIGNAL HEADER



TE Part # 1276565-1
EXTRACTION TOOL FOR .025 REC



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No
Crimp



TE Part # CAT-HPCH5372
HIGH PIN COUNT HEADER



TE Part # CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING



TE Part # 1717396-3
0.64 SMD 16P CAP ASSEMBLY V-TYPE
Tray



TE Part # 1463260-1
DAHT 025 TAB REC G-Tab 22-20 ASSY



TE Part # 2151494-1
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part # 2-2151494-1
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part # 2-2151494-2
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part # 2151494-2
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part # 5-2151494-1
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part # 5-2151494-2
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part # 7-2151494-1
OCEAN_2.0_APPLICATOR-S-055F055F



TE Part # 7-2151494-2
OCEAN_2.0_APPLICATOR-S-055F055F



KIT

REPRESENTATION ONLY


TE Part # 7-2151494-7
[OCEAN_2.0_SPARE_PART_KIT-055F055F](#)



KIT

REPRESENTATION ONLY

TE Part # 7-2836361-7
[OC-140F140F-752-CRIMPTOOLINGKIT](#)



TE Part # 7-1579014-2
[HT11K HAND TOOL TH 0.25 CONTACTS](#)

TE Part # 2-1722368-6
[ISOLATION CRIMP PLATE](#)

Also in the Series | **TH/.025 Connector System**



Automotive Connector Caps & Covers (6)



Automotive Housings(203)



Automotive Seals & Cavity Plugs(2)




Automotive Terminals(25)



Insertion & Extraction Tools(4)



Other Automotive Connector Accessories(5)



PCB Headers & Receptacles(144)

Documents

Product Drawings

025 REC CONTACT

Japanese

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1123343-1_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1123343-1_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1123343-1_M.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

TH/.025 Connector Series

English

Product Specifications

Application Specification

English

Application Specification

Japanese

Crimping .040III Unsealed Contact, Receptacle

Japanese

Crimping of 025 Receptacle Contact

Japanese

Application Specification

Japanese

Crimping of 025 Receptacle Contact

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English

.025 LIGHT SENSOR CONNECTOR

Japanese

Instruction Sheet (non U.S.)

Japanese

.025 LIGHT SENSOR CONNECTOR

Japanese

Instruction Sheet (non U.S.)

Japanese

025/040 IMMOBILIZER CONNECTOR

Japanese

Instruction Sheet (non U.S.)

English

025/040 IMMOBILIZER CONNECTOR

Japanese

Instruction Sheet (non U.S.)

English

025/090II I/O Connector

Japanese



[Instruction Sheet \(non U.S.\)](#)

Japanese

[025/090II I/O Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

English

[Instruction Sheet \(non U.S.\)](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[025/040 I/O Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[025/040 I/O Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[.025 SERIES I/O CONNECTORS \(H-Type 1Row 8Position\)](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[.025 SERIES I/O CONNECTORS \(H-Type 1Row 8Position\)](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[025 Wire to Wire Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[025 Wire to Wire Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

English

[025\(0.64\)/375\(9.5\) HYBRID Connector](#)

English

[Instruction Sheet \(non U.S.\)](#)



English

[025\(0.64\)/375\(9.5\) HYBRID Connector](#)

English

[025 G Wire to Wire Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[025 G Wire to Wire Connector](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[025\(0.64\)/187\(4.8\) I/O CONNECTOR](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese

[025\(0.64\)/187\(4.8\) I/O CONNECTOR](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese