




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
PCB Thickness (Recommended): 1.57 – 2.36 mm [.062 – .093 in]
Mating Tab Width: 6.35 mm [.25 in]
Mating Tab Thickness: .81 mm [.032 in]
PCB Hole Diameter: 1.4 mm [.055 in]

Features

Configuration Features

Stud Hole	No
Terminal Angle	90 °

Body Features

	150 µin
--	---------

Contact Features

Contact Plating Material	Tin
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Contact Underplating Material	Brass
Terminal Size	6.35
Terminal Orientation	Flag

Termination Features



Termination Method to Printed Circuit Board	Through Hole - Solder
Product Terminates To	Printed Circuit Board

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Extension Below Board	3.81 mm[.15 in]
Receptacle Terminal Stock Thickness	.81 mm[.032 in]
PCB Thickness (Recommended)	1.57 – 2.36 mm[.062 – .093 in]
PCB Hole Diameter	1.4 mm[.055 in]
Profile Height from PCB	8.89 mm[.354 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Industry Standards

CSA Certified	Yes
UL Rating	Recognized

Packaging Features

Packaging Quantity	10000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C



Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 63067-1 250 FASTON TAB TPBR	 TE Part # 1217169-1 250 FASTON,PCB TAB,TCBR	 TE Part # 62409-1 250 FASTON TAB TPBR	 TE Part # 1217167-1 250 FASTON,PCB TAB,TCBR
 TE Part # 1217056-1 250 FASTON,PCB TAB,TPBR	 TE Part # 63849-1 250 FASTON TAB TPBR	 TE Part # 1217756-1 187 FASTON,TAB,TNBR	 TE Part # 1742188-1 250 FASTON,PCB TAB,TCBR
 TE Part # 63900-1 250 FASTON TAB TPBR	 TE Part # 1742686-1 250 FASTON,PCB TAB,TCBR	 TE Part # 725996-2 110 FASTON TAB TPBR	 TE Part # 1-725996-2 110 FASTON,FLAG,PCB TAB,TPBR



Also in the Series | FASTON 250



Documents

Product Drawings
250 FASTON,FLAG,PCB TAB,TNBR
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1217754-1_D_c-1217754-1-d.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1217754-1_D_c-1217754-1-d.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1217754-1_D_c-1217754-1-d.3d_stp.zip
English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON PCB Tabs and Receptacles

English

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_1217754-1_06122017145_dmtec

English

MD_1217754-1_06122017145_dmtec

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English