



TE Internal #: 1337772-2
 RF Cable Assemblies, BNC Plug, PVC, Length 3.28 ft [1 m], Black
 Cable, -65 – 165 °C [85 – 329 °F], BNC Plug, BNC, 50 Ω

[View on TE.com >](#)

Cable Assemblies > RF Cable Assemblies



Connector Type (End A): **BNC Plug**
 Jacket Material: **PVC**
 Cable Assembly Length: **1 m [3.28 ft]**
 Cable Color: **Black**
 Operating Temperature Range: **-65 – 165 °C [85 – 329 °F]**

Features

Product Type Features

Coax Cable Type	RG 58C/U
Connector Type (End A)	BNC Plug
Connector Type (End B)	BNC Plug
Cable Assembly Type	BNC

Configuration Features

Number of Connectorized Ends	2
------------------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Plating Material	Nickel
Jacket Material	PVC
Cable Color	Black

Contact Features

Center Contact Plating	Gold
------------------------	------

Usage Conditions

Operating Temperature Range	-65 – 165 °C[85 – 329 °F]
-----------------------------	---------------------------

Other

Cable Assembly Length	1 m[3.28 ft]
-----------------------	--------------



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (3.23% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

50/OHM COAX BNC STR PLUG ELB P

English



Instruction Sheets

GREENPAR RF CONNECTOR CABLE ASSEMBLY INSTRUCTION SHEET

English

Instruction Sheet (non U.S.)

English