




**Buchanan | Buchanan 4 Series**

TE Internal #: 1546940-6

Barrier Strips, Tri-Barrier, Printed Circuit Pin, Wire-to-Board, 8 Position, 8.26 mm [.325 in] Centerline, 1 Row, 300 V, Buchanan 4 Series

[View on TE.com >](#)

Connectors > Terminal Blocks & Strips > Barrier Strips



Barrier Strip Style: **Tri-Barrier**

Bottom Termination Type: **Printed Circuit Pin**

Connector System: **Wire-to-Board**

Number of Positions: **8**

Centerline (Pitch): **8.26 mm [.325 in]**

**Features**

**Product Type Features**

Product Type	Barrier Strip
Block Style	Open Bottom with Standoffs
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

**Configuration Features**

Number of Levels	1
Number of Positions	8
Number of Rows	1

**Electrical Characteristics**

Current Rating (Max)	20 A
Voltage Rating	300 V

**Body Features**

Barrier Strip Style	Tri-Barrier
---------------------	-------------

**Contact Features**

Terminal Material	Copper Alloy
Terminal Plating Material	Tin
Contact Current Rating (Max)	20 A

**Termination Features**



Bottom Termination Type	Printed Circuit Pin
-------------------------	---------------------

### Mechanical Attachment

Mounting Angle	Right Angle
----------------	-------------

Screw Head Type	Wire Clamp Combo Head
-----------------	-----------------------

Top Termination Type	Wire Clamp Combo Head
----------------------	-----------------------

Mounting Insert	With
-----------------	------

Screw Plating Material	Zinc
------------------------	------

Screw Material	Steel
----------------	-------

Mounting Options	End Mounting Ears
------------------	-------------------

Mounting Bushing	With
------------------	------

Mounting Ears	With
---------------	------

Screw Size	4-40
------------	------

Connector Mounting Type	Board Mount
-------------------------	-------------

### Housing Features

Housing Material	Polyamide
------------------	-----------

Centerline (Pitch)	8.26 mm [.325 in]
--------------------	-------------------

### Dimensions

Length	84.1 mm [3.311 in]
--------	--------------------

Wire Size	.326 – 2 mm <sup>2</sup>
-----------	--------------------------

### Usage Conditions

Operating Temperature Range	0 – 105 °C [0 – 221 °F]
-----------------------------	-------------------------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	200
--------------------	-----

Packaging Method	Package
------------------	---------

### Other

Comment	Other options available upon request, consult our Product Information Center.
---------	---



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



Also in the Series | [Buchanan 4 Series](#)



Barrier Strips(72)

## Documents

### Product Drawings

[4PCR-08-008=4PCR ASSY](#)

English

---

### Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#)

English

[1-1773458-2\\_BARRIER\\_STRIPS\\_QUICK\\_REFERENCE\\_GUIDE](#)

English