



Relays, Contactors & Switches > Relays > Signal Relays



Contact Voltage Rating: **120 VAC**
 Signal Relay Mounting Type: **Socket**
 Signal Relay Terminal Type: **Plug-In**
 Signal Relay Coil Voltage Rating: **120 VAC**
 Signal Relay Contact Current Rating: **10 A**

Features

Product Type Features

Relay Style	Power
Product Type	Relay
Relay Type	Control

Electrical Characteristics

Coil Power Rating (AC)	6 VA
Actuating System	AC
Input Voltage	120 VAC
Coil Type	Monostable
Coil Special Features	LED
Contact Voltage Rating	120 VAC
Signal Relay Coil Voltage Rating	120 VAC
Signal Relay Contact Switching Voltage (Max)	120 VAC
Signal Relay Coil Magnetic System	Monostable, AC

Contact Features

Signal Relay Terminal Type	Plug-In
Signal Relay Contact Current Rating	10 A
Signal Relay Contact Arrangement	4 Form C (4PDT)



Contact Number of Poles 4

Termination Features

Termination Type 16 Flat Base Pins

Mechanical Attachment

Signal Relay Mounting Type Socket

Dimensions

Height 118 mm[4.64 in]

Dimensions (L x W x H) (Approximate) 45 x 45 x 109 mm

Length 45 mm[1.772 in]

Width 45 mm[1.722 in]

Usage Conditions

Operating Temperature Range 0 – 60 °C

Operation/Application

Option Coil Energization Light

Packaging Features

Packaging Method Box & Carton

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Not Compliant

EU ELV Directive 2000/53/EC Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
 Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JAN 2022 (223)
 SVHC > Threshold:
 Not Yet Reviewed

Halogen Content Not Yet Reviewed for halogen content

Solder Process Capability Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | [Agastat GP Series](#)



Documents

Product Drawings

[GPIQ=RLY,120VAC,LED](#)

English

Datasheets & Catalog Pages

[5-1773450-5_sec12_GP_ML_TR](#)

English