



Relays, Contactors & Switches > Switches > DIP & SIP Switches



DIP & SIP Switch Product Type: **Switch**

DIP & SIP Switch Contact Mating Area Plating Material: **Gold**

DIP & SIP Switch Housing Color: **Black**

DIP & SIP Switch Housing Material: **Polyphenylene Sulfide (PPS)**

Auto-Insertable: **No**

Features

Product Type Features

DIP & SIP Switch Product Type	Switch
Sealed DIP & SIP Switch	Yes
DIP & SIP Switch Type	DIP
Actuator Style	Recessed Rocker

Configuration Features

Number of Positions	6
Number of Switches	6
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

DIP & SIP Switch Voltage Rating	50 VDC
---------------------------------	--------

Body Features

Seal Type	Tape
-----------	------

Contact Features

Solder Tail Contact Plating	Gold over Nickel
DIP & SIP Switch Contact Mating Area Plating Material	Gold
Auto-Insertable	No
DIP & SIP Switch Contact Current Rating	.1 A
Contact Base Material	Copper Alloy



Termination Features

Termination Style	Outside L
-------------------	-----------

Mechanical Attachment

DIP & SIP Switch Mounting Type	Surface Mount
--------------------------------	---------------

Housing Features

Low Profile	Yes
DIP & SIP Switch Housing Color	Black
DIP & SIP Switch Housing Material	Polyphenylene Sulfide (PPS)
DIP & SIP Switch Centerline	1.27 mm[.05 in]

Dimensions

Length	8.74 mm[.344 in]
--------	------------------

Usage Conditions

Operating Temperature Range	-30 – 85 °C
-----------------------------	-------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
Packaging Quantity	50

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1571983-5 GDH04STR04=DIP SWITCH	 TE Part # 1-1571983-1 GDH08STR04=DIP SWITCH	 TE Part # 1571983-4 GDH04S04=DIP SWITCH	 TE Part # 1977830-4 DIP SWITCH GDH08SA04
 TE Part # 1977830-1 DIP SWITCH GDH02SA04	 TE Part # 1-1571983-7 GDH06STR0N04		

Also in the Series | Alcoswitch DIP

 DIP & SIP Switches(291)	 Rotary Switches(25)	 Switch Seals & Accessories(1)
--	--	--

Also in the Series | Alcoswitch DIP GDH



Documents

Product Drawings

GDH06S04=DIP SWITCH

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1571983-8_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_1571983-8_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1571983-8_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1571983-8_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1571983-8_C.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1571983-8_C.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

Product Environmental Compliance

MD_1571983-8_041320151449_dmtec

1571983-8

DIP & SIP Switches, Switch, Gold, Black Housing, Polyphenylene Sulfide (PPS), Sealed,
6 Switch, -30 – 85 °C, DIP, Alcoswitch DIP



English

[MD_1571983-8_041320151449_dmtec](#)

English