

1577620-1 ✓ ACTIVE

## STRATO-THERM

TE Internal #: 1577620-1

Ring Terminals & Spade Terminals, Ring Tongue, 24 – 22 AWG

Wire Size, .205 – .326 mm<sup>2</sup> Wire Size, Stud Size M4 / #8, STRATO-THERM

[View on TE.com >](#)



Terminals & Splices > Ring Terminals & Spade Terminals



Ring & Spade Terminal Type: **Ring Tongue**

Wire Size: **.205 – .326 mm<sup>2</sup>**

Stud Size: **#8, M4**

Stud Diameter: **4.34 mm [ .171 in ]**

### Features

#### Product Type Features

Shape Description	RING-041
Stud Size	#8, M4
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

#### Configuration Features

Number of Holes	1
Terminal Angle	180 °

#### Electrical Characteristics

Current Rating	1 A
----------------	-----

#### Body Features

Inspection Slot	No
Insulation Sleeve Color	Brown
Weight per Piece	.65 g [.0229 oz]
Stripe Color	Brown

#### Contact Features

Ring & Spade Terminal Type	Ring Tongue
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Nickel



### Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

### Dimensions

Wire Size	.205 – .326 mm <sup>2</sup>
Stud Diameter	4.34 mm[.171 in]
Tongue Thickness	.79 mm[.031 in]
Overall Product Length	21.31 mm[.839 in]
Accepts Wire Insulation Diameter (Max)	1.9 mm[.075 in]
Accepts Wire Insulation Diameter Range	.89 – 1.9 mm[.035 – .075 in]

### Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	260 °C[500 °F]

### Operation/Application

Heavy Duty	No
------------	----

### Industry Standards

Government Qualified	No
----------------------	----

### Packaging Features

Packaging Quantity	1000
Packaging Method	Bag/Box

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 576778  
HHHT PIDG PEEK STRATO 24-22 ASSY



TE Part # 1901611-2  
CCII PIDG STRATO 24-20 ASSY



TE Part # 1901611-1  
CCII PIDG STRATO 24-20 ASSY

### Also in the Series | STRATO-THERM



Ring Terminals & Spade Terminals(96)



Splices(16)

### Documents

**Product Drawings**

[TERMINAL RT PIDG PEEK STRATO 24-22 AWG](#)

English

**CAD Files**

[3D PDF](#)

3D

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1577620-1\\_B.2d\\_dxf.zip](#)

English

**Customer View Model**



[ENG\\_CVM\\_CVM\\_1577620-1\\_B.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1577620-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Product Specifications**

**Application Specification**

English

---

**Product Environmental Compliance**

**TE Material Declaration**

English