




AMP 0.64 Connector System

TE Internal #: 1438426-1

Wire-to-Wire, 2 Position, .1 in [2.54 mm] Centerline, Sealable, Black, Signal, Cable Mount (Free-Hanging), Key A, AMP 0.64 Connector System

[View on TE.com >](#)

Connectors > Automotive Connectors > Connector Housings



Mating Tab Width: .64 mm [.025 in]

Connector System: **Wire-to-Wire**

Number of Positions: 2

Centerline (Pitch): 2.54 mm [.1 in]

Sealable: **Yes**

Features

Product Type Features

Connector Shape	Rectangular
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No

Configuration Features

Number of Positions	2
Number of Rows	1

Body Features

Body Material	Other
Primary Product Color	Black
Connector Code	A

Contact Features

Contact Size	.64mm
Mating Tab Width	.64 mm[.025 in]

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	Without



Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Width	16.45 mm[.648 in]
Product Length	20.61 mm[.811 in]
Product Height	35.3 mm[1.389 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Agency/Standard	SAE/USCAR-2
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	25
Packaging Method	Package

Other

Connector Position Assurance Capable	Yes
--------------------------------------	-----

Product Compliance






[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 638551-3 CONTACT,FEMALE,0.64MM,SN,18-20</p>	 <p>TE Part # 1326028-3 0.64MM FEMALE CONTACT,AU,18-20</p>	 <p>TE Part # 1326028-5 .64MM FEM CONT,AU,18-20,FORMED</p>	 <p>TE Part # 638551-1 CONTACT,FEMALE,0.64MM,SN,18-20</p>
 <p>TE Part # 1326028-2 0.64MM FEMALE CONTACT,AU,22AWG</p>	 <p>TE Part # 638551-4 CONTACT,FEMALE,0.64MM,SN,22</p>	 <p>TE Part # 1326028-1 0.64MM FEMALE CONTACT,AU,18-20</p>	 <p>TE Part # 638551-2 CONTACT,FEMALE,0.64MM,SN,22</p>
 <p>TE Part # 1326028-4 0.64MM FEMALE CONTACT,AU,22AWG</p>	 <p>TE Part # 1326028-6 0.64MM FEMALE CONTACT,AU,22AWG</p>		

Also in the Series | **AMP 0.64 Connector System**

Automotive Connector Caps & Covers
(19)


Automotive Housings(31)



Automotive Terminals(13)



Insertion & Extraction Tools(1)

Other Automotive Connector
Accessories(1)

PCB Headers & Receptacles(38)

Documents

Product Drawings

0.64MM, 2POSN SEALED PLUG, BLA

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1438426-1_C.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1438426-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1438426-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English