

1487594-1 ✓ ACTIVE




TE Internal #: 1487594-1

USB Cable Assemblies, USB 4-Position Plug, Type A to Type B,  
Double-Ended, 28 AWG Wire Size, Black Cable Color, USB Type A  
Plug, USB Type B Plug

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Multimedia Cable Assemblies > USB Cable Assemblies



Cable Assembly Type: **USB 4-Position Plug, Type A to Type B**

Cable Assembly Configuration: **Double-Ended**

Wire Size: **28 AWG**

Cable Color: **Black**

Connector Type (End A): **USB Type A Plug**

## Features

### Product Type Features

Cable Assembly Type	USB 4-Position Plug, Type A to Type B
Connector Type (End A)	USB Type A Plug
Connector Type (End B)	USB Type B Plug
Shielded	Yes

### Configuration Features

Number of USB Connectors	2
Number of Positions	4

### Body Features

Ferrite Core	Without
Equalized	No
Cable Color	Black

### Dimensions

Wire Size	28 AWG
-----------	--------

### Other



Cable Assembly Configuration	Double-Ended
------------------------------	--------------

### Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # 1487594-2 USB, A-B, 28/28, BLACK, 0.25M</p>	 <p>TE Part # 1734366-1 Std USB Type A, VT, T/H</p>	 <p>TE Part # 5353929-1 Std USB Type A, R/A, SMT, Offset, Panel</p>	 <p>TE Part # 5787617-1 RECP ASSY, R/A, STACKED, THRU-HOLE, USB,</p>
--	--	--	---



## Documents

### Product Drawings

[USB, A-B, 28/28, BLACK, 0.5M](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1487594-1\\_H.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1487594-1\\_H.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1487594-1\\_H.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Environmental Compliance

[MD\\_1487594-1\\_08122017451\\_dmtec](#)

English

[MD\\_1487594-1\\_08122017451\\_dmtec](#)

English