

1658608-1 ✓ ACTIVE

AMPLIMITE | AMPLIMITE HDF

TE Internal #: 1658608-1

IDC D-Sub Connectors, Plug, 28 – 26 AWG Solid Wire Size, .1 – .13 mm<sup>2</sup> Solid Wire Size, Shielded, Cable-to-Cable, 37 Position, AMPLIMITE HDF

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm



Connector & Housing Type: **Plug**

Solid Wire Size: .1 – .13 mm<sup>2</sup>

Shielded: **Yes**

Connector System: **Cable-to-Cable**

[All IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm \(17\)](#)

## Features

### Product Type Features

Profile	Low
Grounding Indents	With
Grade	Standard
Thread Type	Standard
Shell Type	Front Metal Shell
Protective Cover	With
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
Connector Product Type	Connector Assembly
D-Sub Shell Size	4
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features



Number of Positions	37
Number of Rows	2
Compatible With Wire & Cable Type	Ribbon Cable

### Body Features

Strain Relief Part Number	747275-1
Shell Plating Finish	Bright
Color	Black
Cable Exit Angle	90°
Shell Plating Material	Tin
Ribbon Cable Centerline Spacing	1.27 mm [.05 in]
Insert Material	Brass
Shell Material	Steel

### Contact Features

Contact Type	Pin
	30 μin
Contact Mating Area Plating Material	Gold, Gold Flash over Palladium Nickel
Contact Underplating Material	Nickel, Palladium Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
D-Sub Contact Size	20
Contact Current Rating (Max)	1.25 A

### Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

### Mechanical Attachment

Mating Connector Lock	With
Mounting Angle	Straight
Mating Connector Lock Type	Threaded Insert, 4-40 UNC
Threaded Insert Material	Steel
Threaded Insert Plating Material	Zinc
PCB Mount Retention Type	None
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

--	--



Housing Material	Thermoplastic
Housing Color	Black
Enclosure	Without
Centerline (Pitch)	2.77 mm[.109 in]

### Dimensions

Cable Insulation Diameter Range	.81 – .97 mm[.032 – .038 in]
Solid Wire Size	.1 – .13 mm <sup>2</sup>
Wire Size	.08 – .15 mm <sup>2</sup>

### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Shielded	Yes
Circuit Application	Signal

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	40
Packaging Method	Tube

### Other

Optional Cable Stabilizer	747275-1
Comment	All plug assemblies are supplied with housing and cover preassembled

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (3.7% in Component Part) <small>Article Safe Usage Statements:</small>



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-023-DRARS4277  
D-Sub Receptacle Assembly: Right Angle, Shell Size 4, 2.77mm




TE Part # CAT-AM7-253  
IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm



TE Part # CAT-026-RAVSAP4277  
D-Sub Receptacle Assembly: Vertical, Action Pin, Shell Size 4, 2.77mm



TE Part # CAT-AM7-248H5  
IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm



TE Part # CAT-025-DRAVS4277  
D-Sub Receptacle Assembly: Vertical, Shell Size 4, 2.77mm




TE Part # 2-1393480-0  
V23529B1121B237=SUB D FEDERLEI



TE Part # 3-1392010-7  
V23529B1225B237=SUB D FEDERLEI



TE Part # 7-1393740-3  
V42254A2216B237=SUB D FEDERLEI



TE Part # 768340-1  
UNIV HAND TOOL KIT AMPLATCH



TE Part # 3-1392010-8  
V23529B1122B237=SUB D FEDERLEI



TE Part # 7-338316-2  
37P.HDP20 REC ASSY



TE Part # 8-338316-2  
37P.HDP20 REC ASSY

Also in the Series | **AMPLIMITE HDF**



D-Sub Locking &amp; Mounting(8)



IDC D-Sub Connectors(36)

## Documents

### Product Drawings

[37 POS HDF PLUG, MS, LEAD FREE](#)

English

### CAD Files

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_1658608-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1658608-1\\_A.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1658608-1\\_A.2d\\_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

### Product Specifications

[Product Specification](#)

English

[Product Specification](#)

English

### Product Environmental Compliance

[MD\\_1658608-1\\_05292013634\\_dmtec](#)

English

[MD\\_1658608-1\\_05292013634\\_dmtec](#)

English



[Agency Approvals](#)

[UL Report](#)

English