

1546746-4 ✓ ACTIVE

AMP | AMP CPC

TE Internal #: 1546746-4

Unscreened Circular Connector Backshells & Clamps, Cable Clamp, Size 11, Right Angle, Protective Cover, Bag, 3/4-20 UNEF-2B, AMP CPC

[View on TE.com >](#)



Connectors > Circular Connectors > Circular Connector Accessories > Unscreened Circular Connector Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Clamp**

Compatible With Circular Connector Shell Size: **11**

Body Orientation: **Right Angle**

Accepts Cable Diameter (Max): **11.51 mm [.453 in]**

Protective Cover: **With**

Features

Product Type Features

Product Type	Accessory
Backshell & Clamp Accessory Type	Cable Clamp
Protective Cover	With

Body Features

Strain Relief Type	Right Angle
Strain Relief Color	Black
Cable Clamp Material	Nylon
Strain Relief Material	Thermoplastic
Cable Clamp Color	Black

Mechanical Attachment

Screw & Hole Thread Size	3/4-20 UNEF-2B
--------------------------	----------------

Housing Features

Body Orientation	Right Angle
------------------	-------------



Dimensions

Accepts Cable Diameter (Max)	11.51 mm[.453 in]
------------------------------	-------------------

Operation/Application

Compatible With Circular Connector Shell Size	11
---	----

Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Other

Comment	Screw finish is zinc plated non-hexavalent chromate, With Cover.
---------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability











Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP CPC



Documents

Product Drawings

R/A CABLE CLAMP KIT,SZ 11, MINI CPC

English

CAD Files

Customer View Model

ENG_CVM_1546746-4_C.3d_igs.zip

English



Customer View Model

[ENG_CVM_1546746-4_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1546746-4_C.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_CVM_1546746-4_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1546746-4_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1546746-4_C.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773902-9_CPC_Catalog](#)

German

[1-1773902-9_CPC_Catalog](#)

English

[1-1773902-9_CPC_Catalog](#)

[1-1773902-9_CPC_Catalog](#)

Japanese

[AMP Circular Connectors for Commercial Signal & Power Applications Continued](#)

English