



Wire Protection & Management > Heat Shrink Shapes > Sealing Sleeves



Sealing Sleeve Product Type: **Heat Shrink Tubing**
Expanded Inside Diameter (Min): [**.5 in**]
Recovered Inside Diameter (Max): [**.25 in**]
Primary Product Color: **Black**
Primary Product Material: **Polyolefin**

Features

Product Type Features

Shell Size	8
Sealing Sleeve Product Type	Heat Shrink Tubing

Body Features

Strain Relief Color	Black
Strain Relief Material	Polyamide
Primary Product Color	Black
Primary Product Material	Polyolefin

Dimensions

	.25 in
--	--------

Usage Conditions

Operating Temperature Range	-55 – 110 °C
-----------------------------	--------------

Other

Comment	Heat Shrinkable
---------	-----------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-C83998EE
Mini Circular Plastic Connectors (CPC)

Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)




Circular Connector Seals(36)



Circular Power Connectors(467)



Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Documents

Product Drawings

STR RLF ASSY,TUBING,SIZE 8

English

CAD Files

Customer View Model

ENG_CVM_1546997-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_1546997-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_1546997-1_A.2d_dxf.zip

English

3D PDF

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1546997-1_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1546997-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1546997-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773902-9_CPC_Catalog](#)

German

[1-1773902-9_CPC_Catalog](#)

English

[1-1773902-9_CPC_Catalog](#)

[1-1773902-9_CPC_Catalog](#)

Japanese

[AMP Circular Connectors for Commercial Signal & Power Applications Continued](#)

English