

1563111-1 ✓ ACTIVE

AMP | Heavy Duty Sealed Connector Series

TE Internal #: 1563111-1

Automotive Connector Caps & Covers, Cover - Cable Exit, Cable Exit Angle 180° (In-Line), Black, PA, Heavy Duty Sealed Connector Series

[View on TE.com >](#)



Connectors > Automotive Connectors > Connector Accessories > Connector Caps & Covers > Heavy Duty Sealed Connector Series Backshells



Protection & Strain Relief Accessory Type: **Cover - Cable Exit**

Cable Exit Angle: **180° (In-Line)**

Strain Relief: **With**

Primary Product Color: **Black**

Primary Product Material: **PA**

[All Heavy Duty Sealed Connector Series Backshells \(8\)](#)

## Features

### Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
Connector System	Wire-to-Board, Wire-to-Device

### Configuration Features

Number of Positions	8, 10, 12
---------------------	-----------

### Body Features

Cable Exit Angle	180° (In-Line)
Primary Product Color	Black
Primary Product Material	PA

### Mechanical Attachment

Strain Relief	With
---------------	------

### Dimensions

Compatible Cable Bundle Diameter Range	12.7 mm[.5 in]
--	----------------



### Usage Conditions

Compatible With Connector Style	Housing For Female Terminals, Housing For Male Terminals
Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	700
Packaging Method	Box

### Other

Serviceable	Yes
-------------	-----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-H3399-CH8172  
Heavy Duty Sealed Connector Series Housings



TE Part # 9-2331355-1  
HD MATEnet 1+6 REC. HSG ASSY, GRP D



TE Part # 9-2331355-2  
HD MATEnet 1+6 REC. HSG ASSY, GRP D



TE Part # 9-2331355-3  
HDSENET 1+6 REC. HSG ASSY D



TE Part # 9-2331355-4  
HDSENET 1+6 REC. HSG ASSY D



TE Part # 9-2334935-1  
HD MATEnet 1+6 TAB HSG. ASSY, GRP D



TE Part # 9-2334935-2  
HD MATEnet 1+6 TAB HSG. ASSY, GRP D



TE Part # 9-2334935-3  
HDSENET 1+6 TAB HSG ASSY D



TE Part # 9-2334935-4  
HDSENET 1+6 TAB HSG ASSY D



TE Part # 9-2348772-1  
HD MATEnet 3+0 TAB HSG ASSY, GRP E



TE Part # 9-2348772-2  
HD MATEnet 3+0 TAB HSG ASSY, GRP E



TE Part # 9-2348776-1  
HD MATEnet 3+0 REC HSG ASSY, GRP E



TE Part # 9-2348776-2  
HD MATEnet 3+0 REC HSG ASSY, GRP E



TE Part # 9-2348782-1  
HD MATEnet 2+6 TAB HSG ASSY, GRP E



TE Part # 9-2348782-2  
HD MATEnet 2+6 TAB HSG ASSY, GRP E



TE Part # 9-2348786-1  
HD MATEnet 2+6 REC HSG ASSY, GRP E



TE Part # 9-2348786-2  
HD MATEnet 2+6 REC HSG ASSY,  
GRP E



TE Part # 9-2348789-1  
HD MATEnet 2+6 TAB ASSY, GRP E,  
FLANGED



TE Part # 9-2348789-2  
HD MATEnet 2+6 TAB ASSY, GRP E,  
FLANGED




TE Part # 9-2348792-1  
HD MATEnet 1+12 TAB HSG ASSY,  
GRP E


## Also in the Series | Heavy Duty Sealed Connector Series




Automotive Connector Caps & Covers  
(25)



Automotive Housings(207)




Automotive Seals & Cavity Plugs(5)



Data Connectivity Headers(2)



Data Connectivity Housings(18)



Other Automotive Connector  
Accessories(34)



PCB Headers & Receptacles(1)

## Documents

### Product Drawings

**COVER,180**

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1563111-1\\_G.2d\\_dxf.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1563111-1\\_G.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1563111-1\\_G.3d\\_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Datasheets & Catalog Pages

### HDSCS Catalog

English

### ICT Terminals and Connectors Catalogue

English

### CONNECTOR SELECTOR

English

---

## Product Specifications

### Application Specification

English