




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire Stop	No
Wire/Cable Type	Regular Wire
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Accepts Wire Insulation Diameter Range	2.2 – 3.4 mm [.086 – .134 in]
Overall Length	25.8 mm [1.01 in]
Receptacle Terminal Stock Thickness	.4 mm [.016 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Packaging Features

Packaging Quantity	3500
Packaging Method	Strip/Reel

Other

Comment	Air-feed Applicator should be used.
---------	-------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 172076-6 POSITIVE LOCK 250 HOUSING RECEPTACLE	 TE Part # 172076-1 POSITIVE LOCK 250 HOUSING RECEPTACLE	 TE Part # 2-172076-1 250 HSG. PL MKII REC. NAT	 TE Part # 1969864-1 2P, 250 SERIES, POSITIVE LOCK MARK II
 TE Part # 2-521229-1 PL EXII & FASTON 250 HSG 2P NAT	 TE Part # 724659-2 EXT TOOL FOR POSITIVE .250	 TE Part # 2-172076-6 PL 250 REC HSG 1P NYLON BLUE	 TE Part # 2-172076-7 POSITIVE LOCK 250 HOUSING RECEPTACLE
 TE Part # 172076-2 PL MKII 250 REC HSG 1P NYLON BLACK	 TE Part # 2-172076-2 POSITIVE LOCK 250 HOUSING RECEPTACLE	 TE Part # 178833-1 POSITIVE LOCK .250 HOUSING RECEPTACLE	 TE Part # 521229-1 PL 250 HOUSING RECEPTACLE NYLON 6/6
 TE Part # 177627-1 PL .250 (6.3 MM) HOUSING RECEPTACLE	 TE Part # 172076-7 PL MKII 250 REC HSG 1P NYLON RED	 TE Part # 174429-1 PL 250 HOUSING RECEPTACLE	 TE Part # 177627-7 PL .250 (6.3 MM) HOUSING RECEPTACLE



TE Part # 1969820-1
250 HIGH TEMP POS LOCK HSG LCP

TE Part # 2150061-2
OCEAN_2.0_Applicator-E-110F170F

TE Part # 172076-4
POSITIVE LOCK 250 HOUSING RECEPTACLE

TE Part # 172076-5
POSITIVE LOCK 250 HOUSING RECEPTACLE

Also in the Series | Positive Lock 250

Automotive Terminals(1)

Crimp Terminal Housings(202)

Insertion & Extraction Tools(3)

Insulation Boots & Sleeves(4)

Quick Disconnects(189)

Documents

Product Drawings

250 PL MKII REC. 18-14AWG PTBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170328-1_AB.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170328-1_AB.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170328-1_AB.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

POS_LOCK_MIL_QRG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_170328-1_111620181045_dmtec

English

MD_170328-1_111620181045_dmtec

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

AMP* POSITIVE LOCK CONNECTOR

English

Agency Approvals

Agency Approval Document

English