

1734028-1 ✓ ACTIVE


TE Internal #: 1734028-1

USB Connectors, A, 2.0, Standard Profile, Plug, 1 Port, Top, Right Angle, Tape & Reel / Box & Tray, Flush, Surface Mount, Cable-to-Board, 1500

[View on TE.com >](#)



Connectors > Audio & Video Connectors > USB Connectors



USB Adapter Type: **A**

USB Version: **2.0**

Connector Profile: **Standard**

Connector & Housing Type: **Plug**

Number of Ports: **1**

## Features

### Product Type Features

USB Adapter Type	A
USB Version	2.0
Connector & Housing Type	Plug
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
USB Connector Type	USB 2.0 Type-A

### Configuration Features

Number of Mounting Legs	2
Number of Ports	1
Number of Positions	4

### Body Features

Shell Plating Material	Nickel over Copper
Connector Profile	Standard

### Contact Features

--	--



Contact Mating Area Plating Material Thickness	.76 $\mu\text{m}$ [29.92 $\mu\text{in}$ ]
Contact Mating Area Plating Material	Gold Flash over Palladium Nickel
Contact Current Rating (Max)	1.5 A

#### Termination Features

Termination Post & Tail Length	1.2 mm[.047 in]
Termination Method to Printed Circuit Board	Surface Mount

#### Mechanical Attachment

Locking Feature	Without
PCB Mount Alignment Type	Locating Posts
PCB Mount Location	Top
PCB Connector Seating	Flush
PCB Mount Retention Type	Straight Leg
Connector Mounting Type	Board Mount

#### Housing Features

Housing Material	Thermoplastic
Housing Color	Natural
Body Orientation	Right Angle
Centerline (Pitch)	2 mm, 2.5 mm[.078 in][.098 in]

#### Dimensions

PCB Thickness (Recommended)	1.6 mm[.063 in]
-----------------------------	-----------------

#### Usage Conditions

Soldering Temperature (Max)	260 $^{\circ}\text{C}$ [500 $^{\circ}\text{F}$ ]
Mating Cycles (Max)	1500
Operating Temperature Range	-55 – 85 $^{\circ}\text{C}$ [-67 – 185 $^{\circ}\text{F}$ ]

#### Operation/Application

Halogen Free	No
Circuit Application	Power & Signal

#### Industry Standards

Moisture Sensitivity Level	5a
Industry Standard	USB 2.0
UL Flammability Rating	UL 94V-0

#### Packaging Features



Packaging Quantity	3200
Packaging Method	Box & Tray, Tape & Reel

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 5787617-3  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 1775690-2  
Std USB Type A, VT, T/H, 2.5A



TE Part # 5787617-4  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 1-292303-1  
Std USB Type A, R/A, SMT

 <p>TE Part # 292303-5 Std USB Type A, R/A, T/H, Natural</p>	 <p>TE Part # 5787745-5 USB A R/A STAK ASSY THRU HOLE</p>	 <p>TE Part # 1734366-3 Std USB Type A, VT, T/H, Blue</p>	 <p>TE Part # 5787745-1 USB A R/A STAK ASSY THRU HOLE</p>
 <p>TE Part # 1734366-4 Std USB Type A, VT, T/H</p>	 <p>TE Part # 5787617-8 RECP ASSY, R/A, STACKED, THRU-HOLE, USB,</p>	 <p>TE Part # 292303-3 Std USB Type A, R/A, T/H, Natural</p>	 <p>TE Part # 5787745-2 USB A R/A STAK ASSY THRU HOLE</p>
 <p>TE Part # 1734366-1 Std USB Type A, VT, T/H</p>	 <p>TE Part # 5353928-2 Std USB Type A, R/A, SMT, Offset, Panel</p>	 <p>TE Part # 5353929-1 Std USB Type A, R/A, SMT, Offset, Panel</p>	 <p>TE Part # 5787745-4 USB A R/A STAK ASSY THRU HOLE</p>
 <p>TE Part # 1-1734775-1 Std USB Type A, Flag, T/H, 1.8A</p>	 <p>TE Part # 292303-1 Std USB Type A, R/A, T/H</p>	 <p>TE Part # 5787617-1 RECP ASSY, R/A, STACKED, THRU-HOLE, USB,</p>	 <p>TE Part # 292303-7 Std USB Type A, R/A, SMT, Offset, Natural</p>

## Documents

### Product Drawings

Std USB Type A, Plug, Natural

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1734028-1\\_C.2d\\_dxf.zip](#)

English

[3D PDF](#)

[3D](#)



### Customer View Model

[ENG\\_CVM\\_CVM\\_1734028-1\\_C.3d\\_igs.zip](#)

English

### Customer View Model

[ENG\\_CVM\\_CVM\\_1734028-1\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[USB Quick Reference Guide \(English\)](#)

English

[USB and Mini USB Datasheet 7-1773442-0](#)

English

### Product Specifications

[Crimping Drawer Connector Contacts](#)

English

[Application Specification](#)

English