

1651813-1 ✓ ACTIVE

TE Internal #: 1651813-1

Rectangular Connector Adapters, Adapter, None, None, -40 – 221 °

F [-40 – 105 °C]

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Adapters



Rectangular Connector Adapter Type: **Adapter**

Agency/Standard: **None**

UL Flammability Rating: **None**

Sealable: **No**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

## Features

### Product Type Features

Rectangular Connector Adapter Type	Adapter
Sealable	No

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Industry Standards

Agency/Standard	None
UL Flammability Rating	None

### Packaging Features

Packaging Quantity	100
Packaging Method	Bag

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022  
(224)Candidate List Declared Against: JUN 2012  
(84)

SVHC &gt; Threshold:

Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

## CAD Files

## Customer View Model

[ENG\\_CVM\\_CVM\\_1651813-1\\_A.2d\\_dxf.zip](#)

English

## 3D PDF

3D

## Customer View Model

[ENG\\_CVM\\_CVM\\_1651813-1\\_A.3d\\_igs.zip](#)

English

## Customer View Model

[ENG\\_CVM\\_CVM\\_1651813-1\\_A.3d\\_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications

### Product Specification

English