




Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**
Operating Voltage: **50 VAC, 300 VAC**
Contact Mating Area Plating Material: **Tin**
Wire Size: **.5 – 1.42 mm²**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	50 VAC, 300 VAC
Insulation Resistance	1000

Contact Features

Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	12 A
Contact Type	Receptacle
Contact Retention Within Housing	With
Mating Tab Width	1.2 mm[.047 in]
Mating Tab Thickness	.64 mm[.025 in]
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material Thickness	.8 µm[31.49 µin]



Wire Contact Termination Area Plating Thickness	.8 µm[31.49 µin]
Wire Contact Termination Area Plating Material	Pre-Tin
Wire Contact Termination Area Plating Material Finish	Matte
Contact Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	Without

Dimensions

Wire Size	.5 – 1.42 mm²
Accepts Wire Insulation Diameter Range	1.7 – 3.3 mm[.067 – .13 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Method	Bag & Box
Packaging Quantity	1000

Other

Wire/Cable Type	Discrete Wire
Wire Type	Stranded
For Use With	Plug Housing

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 176280-9 UNIV POWER PLUG HSG 18P F/H	 TE Part # 176275-1 UNIV POWER PLUG HSG 8P F/H	 TE Part # 176276-1 AMP UNIVERSAL POWER PLUG 9P	 TE Part # 176278-9 UNIV POWER PLUG HSG 12P F/H
 TE Part # 178481-1 UP 3.96 4P PLUG HSG NATRL	 TE Part # 178483-1 UP 3.96 6P PLUG HSG NATRL	 TE Part # 178482-1 UP 3.96 5P PLUG HSG NATRL	 TE Part # 178125-1 U/POWER PLUG HSG 2P 7.92M/M







TE Part # 176273-1
AMP UNIVERSAL POWR PLUG 4P




TE Part # 176272-1
AMP UNIVERSAL POWER PLUG 3P



TE Part # 176270-1
UNIV POWER PLUG HSG 1P F/H



TE Part # 176271-1
AMP UNIVERSAL POWER PLUG 2P



TE Part # 178125-4
U/POWER PLUG HSG 2P 7.29MM



TE Part # 176279-1
UNIV POWER PLUG HSG 15P F/H



TE Part # 176279-9
UNIV POWER PLUG HSG 15P F/H



TE Part # 4-178842-1
AMP U/P SGL ROW PLUG HSG 4P




TE Part # 913923-1
EXTRACTON TOOL FOR 175150



TE Part # 6-178842-1
AMP U/P SGL ROW PLUG HSG 6P



TE Part # 176274-1
AMP UNIVERSAL POWER PLUG 6P



TE Part # 176271-4
AMP UNIVERSAL POWER PLUG 2P


Also in the Series | AMP Universal Power



Connector Contacts(1)



Insertion & Extraction Tools(1)



Power Contacts(21)



Rectangular Power Connectors(177)

Documents

Product Drawings
UNIV POWER REC CONT L/P
English

CAD Files
3D PDF
3D
Customer View Model



[ENG_CVM_CVM_175156-1_R.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_175156-1_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_175156-1_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of Universal Power Contact

English

Product Specification

Japanese

AMP Universal Power Connector

Japanese

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Extraction Tool for UP(913923-1)

English

Instruction Sheet (non U.S.)

English

AMP UNIVERSAL POWER CONNECTOR SERIES

English

Instruction Sheet (non U.S.)

English

Hand Tool, PN 914181-1, Universal Power Contact (Was IS-505J)

Japanese

Instruction Sheet (non U.S.)

English