

175269-1 ✓ ACTIVE

AMP | Multilock Connector System


TE Internal #: 175269-1

Automotive Terminals, Receptacle, Mating Tab Width .071 in [1.8 mm], Tab Thickness .025 in [.64 mm], 20 – 16 AWG Wire Size, Multilock Connector System

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > MULTILOCK, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **1.8 mm [.071 in]**

Mating Tab Thickness: **.64 mm [.025 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Wire Size: **20 – 16 AWG**

[All MULTILOCK, RECEPTACLE AND TAB \(142\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	1.8mm
Contact Fabrication	Stamped & Formed
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	1.8 mm[.071 in]
Mating Tab Thickness	.64 mm[.025 in]
Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Wire Size	.5 – 1.25 mm ²
-----------	---------------------------



Wire Size Search	16 AWG, 17 AWG, 18 AWG, 19 AWG, 20 AWG
------------------	--

Wire Insulation Diameter	1.8 – 2.6 mm [.071 – .102 in]
--------------------------	-------------------------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C [176 °F] [185 °F][194 °F][212 °F][221 °F]
-----------------------------	---

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Packaging Features

Packaging Method	Reel
------------------	------

Packaging Quantity	4000
--------------------	------

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING



TE Part # 2-2266011-1
OCEAN_2.0_Applicator-S-080F110F



TE Part # 2-2266011-2
OCEAN_2.0_Applicator-S-080F110FA



TE Part # 2266011-1
OCEAN_2.0_Applicator-S-080F110F



TE Part # 2266011-2
OCEAN_2.0_Applicator-S-080F110FA



TE Part # 7-2266011-1
OCEAN_2.0_Applicator-S-080F110F



TE Part # 7-2266011-2
OCEAN_2.0_Applicator-S-080F110FA



KIT
REPRESENTATION ONLY


TE Part # 7-2266011-7
OCEAN_2.0_SPARE_PART_KIT-080F110F




TE Part # 90654-1
PRO-CRIMPER ASSY MULTILOCK



TE Part # 937312-1
EXT-TOOL



TE Part # 917992-6
HYBRID MK-2 PLUG HSG ASSY 26P



TE Part # 175368-2
SCCS M-II PLUG ASSY 14P



TE Part # 175371-2
SCCS M-II PLUG ASSY 20P



REPRESENTATION ONLY







TE Part # 934196-1
DAHT 070II M REC TAB 20-16 ASSY



TE Part # 177698-1
IMPUL MATE PLUG HSG ASSY 48P



Also in the Series | Multilock Connector System



Documents

Product Drawings
[070 REC \(M\) FOR NSCC](#)

Japanese

CAD Files

[3D PDF](#)

English

[Customer View Model](#)



[ENG_CVM_175269-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_175269-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_175269-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MULTILOCK Connector System](#)

English

Product Specifications

[Application Specification](#)

English

[Crimping .070II Series Tab and Receptacle Contact](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[Description in Japanese](#)

English

[Instruction Sheet \(non U.S.\)](#)

Japanese