



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts > DYNAMIC 3000 CONTACT



Contact Type: **Tab**  
Connector System: **Component-to-Wire**  
Wire Size: **.08 – .24 mm<sup>2</sup>**  
Contact Mating Area Plating Material: **Gold**

[All DYNAMIC 3000 CONTACT \(91\)](#)

Features

Product Type Features

|                                   |                   |
|-----------------------------------|-------------------|
| Connector System                  | Component-to-Wire |
| Connector & Contact Terminates To | Wire & Cable      |

Contact Features

|                                      |                 |
|--------------------------------------|-----------------|
| Mating Tab Width                     | 2 mm[.08 in]    |
| Mating Tab Thickness                 | .64 mm[.025 in] |
| Contact Type                         | Tab             |
| Contact Mating Area Plating Material | Gold            |
| Contact Current Rating (Max)         | 15 A            |

Dimensions

|           |                           |
|-----------|---------------------------|
| Wire Size | .08 – .24 mm <sup>2</sup> |
|-----------|---------------------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Packaging Features

|                  |           |
|------------------|-----------|
| Packaging Method | Bag & Box |
|------------------|-----------|



Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JUNE 2022 (224)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-D9934-A75B  
Receptacle and Tab Housing: 5.08 mm Pitch, 250-600V

TE Part # CAT-D9934-A75A  
DYNAMIC 3100 REC AND TAB HSG

TE Part # 234168-1  
EXTRACTION TOOL(DYNAMIC D-3)

TE Part # CAT-D9934-A75C  
DYNAMIC 3500 REC AND TAB HSG



TE Part # 91565-1  
CCII D-3 S REC TAB 28-24 ASSY

TE Part # 2381453-1  
SDE F DYNAMIC D3000 28-24AWG ASSY

TE Part # 2381453-2  
SDE F DYNAMIC D3000 28-24AWG DIE SET

TE Part # 90682-2  
PROCRIMPER DIE ASSY DYNAMIC

TE Part # 2255145-1  
MINI SAHT D3000-S

TE Part # 90682-1  
PRO-CRIMPER ASSEMBLY

Also in the Series | Dynamic 3000 Series

Connector Contacts(3)

Insertion & Extraction Tools(1)

PCB Connector Keying(1)

PCB Connector Mounting(8)

PCB Headers & Receptacles(283)

PCB Terminal Blocks(25)

Standard Rectangular Connectors(2)

Wire-to-Board Connector Assemblies & Housings(152)

Wire-to-Board Connector Contacts(91)

Documents



Product Drawings

DYNAMIC D-3 TAB CONT. S AU 0.76 L/P

English

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_175287-3\_O.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_175287-3\_O.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_175287-3\_O.2d\_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773732-4\_DYNAMIC\_SERIES\_CATALOG\_ENGLISH

Japanese

1-1773732-4\_DYNAMIC\_SERIES\_CATALOG\_ENGLISH

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

English

Agency Approvals

TUV Certificate

English