




TE Internal #: 170204-4

Connector Contact, Socket, Wire-to-Board / Wire-to-Wire, 26 – 20 AWG Wire Size, .12 – .5 mm² Wire Size, Gold, Loose Piece, Wire & Cable, 2 A, Signal

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Socket**

Connector System: **Wire-to-Board, Wire-to-Wire**

Wire Size: **.12 – .5 mm²**

Contact Mating Area Plating Material: **Gold**

Features

Product Type Features

Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	750 VAC
Insulation Resistance	500 MΩ
Operating Voltage	250 VAC

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
	15 μin
Contact Base Material	Phosphor Bronze
Contact Type	Socket
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	2 A

Mechanical Attachment



Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Dimensions

Accepts Wire Insulation Diameter Range	1.09 – 1.91 mm [.043 – .075 in]
Wire Size	.12 – .5 mm²

Usage Conditions

Operating Temperature Range	-20 – 105 °C [-4 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 354940-1 PRO-CRIMPER III FRAME W/O DIES	 TE Part # 171822-8 EIS REC. HSG 8P-NATURAL	 TE Part # 171822-6 EIS REC. HSG 6P-NATURAL	 TE Part # 171822-7 EIS REC. HSG 7P-NATURAL
 TE Part # 1-171822-2 EIS REC. HSG 12P-NATURAL	 TE Part # 171822-5 EIS REC. HSG 5P-NATURAL	 TE Part # 171822-9 EIS REC. HSG 9P-NATURAL	 TE Part # 171822-3 EIS REC. HSG 3P-NATURAL
 TE Part # 171822-2 EIS REC. HSG 2P-NATURAL	 TE Part # 1-171822-0 EIS REC. HSG 10P-NATURAL	 TE Part # 171822-4 EIS REC. HSG 4P-NATURAL	 TE Part # 172486-2 2P REC HSG CRIMP EI SER
 TE Part # 2-171822-3 EIS REC. HSG 3P-BLACK	 TE Part # 2-171822-4 EIS REC. HSG 4P-BLACK	 TE Part # 4-171822-5 EIS REC. HSG 5P-BLUE	 TE Part # 91556-1 CCII AMP EI SERIES 26-20 ASSY
 TE Part # 4-171822-4 EIS REC. HSG 4P-BLUE	 TE Part # 172486-3 3P REC HSG CRIMP EI SER	 TE Part # 4-171822-8 E.I.SERIES CONN REC 8P	 TE Part # 4-172486-2 2P REC HSG CRIMP EI SERBLUE

Documents



Product Drawings

170262-4 LP E1CRIMP SNAP IN

English

CAD Files

Customer View Model

ENG_CVM_CVM_170204-4_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170204-4_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170204-4_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773972-5_EIS_Connectors_Brochure

English

Product Specifications

Crimping of AMP EI Series Connector Contacts

Japanese

Application Specification

Japanese

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

AMP "EI" Series Connector

English

Instruction Sheet (non U.S.)

English

Agency Approvals

Agency Approval Document

English